



SU1000RTLCD2U Estimated Runtime

| UPS | Extended Battery Module | EBM QTY | CONNECTED EQUIPMENT LOAD IN WATTS | | | | | | | | | | | | | |
|---------------|-------------------------|---------|-----------------------------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-------|------|------|------|
| | | | 200 | 300 | 350 | 400 | 450 | 500 | 550 | 600 | 650 | 700 | 750 | 800 | 850 | 900 |
| SU1000RTLCD2U | Internal batteries | 0 | 45 | 29 | 25 | 21 | 18 | 16 | 14 | 12 | 11 | 10 | 8.5 | 7.7 | 6.9 | 6.3 |
| SU1000RTLCD2U | BP36RT | 1 | 138 | 89 | 75 | 64 | 56 | 50 | 44 | 40 | 36 | 33 | 30.0 | 28.0 | 26.0 | 24.0 |
| SU1000RTLCD2U | BP36RT | 2 | 248 | 161 | 135 | 116 | 101 | 89 | 79 | 71 | 64 | 59 | 54.0 | 50.0 | 46.0 | 43.0 |
| SU1000RTLCD2U | BP36RT | 3 | 370 | 239 | 201 | 172 | 150 | 132 | 117 | 105 | 95 | 87 | 80.0 | 74.0 | 68.0 | 64.0 |
| SU1000RTLCD2U | BP36RT | 4 | 501 | 324 | 272 | 233 | 203 | 178 | 159 | 143 | 129 | 118 | 108.0 | 99.0 | 92.0 | 86.0 |

All runtime values are shown in minutes.