



SU1000XLa Estimated Runtime

Load in Watts

UPS	Battery Pack	20W	40W	60W	80W	100W	200W	300W	400W	500W	600W	700W	800W
SU1000XLa	Internal Batteries	180	126	96	76	63	31	20	14	10	8.0	6.4	4.5
SU1000XLa	1 BP24V15RT2U	462	332	256	207	172	89	58	42	31	25	20	17
SU1000XLa	1 BP24V28-2U	793	579	452	368	309	165	108	79	60	47	39	33
SU1000XLa	1 BP24V70-3U	1,749	1,303	1,034	854	725	404	272	202	156	125	104	89
SU1000XLa	2 BP24V70-3U	3,991	3,061	2,478	2,078	1,787	1,040	722	549	432	353	297	256
SU1000XLa	3 BP24V70-3U	5,524	4,310	3,529	2,984	2,583	1,533	1,077	826	655	540	457	395
SU1000XLa	4 BP24V70-3U	6,865	5,434	4,493	3,827	3,330	2,008	1,424	1,100	876	725	617	535
SU1000XLa	5 BP24V70-3U	8,047	6,452	5,381	4,612	4,033	2,467	1,762	1,368	1,094	909	775	674
SU1000XLa	6 BP24V70-3U	9,098	7,378	6,201	5,345	4,695	2,909	2,091	1,630	1,309	1,091	932	813
SU1000XLa	7 BP24V70-3U	10,038	8,223	6,961	6,032	5,320	3,335	2,413	1,888	1,521	1,270	1,088	950
SU1000XLa	8 BP24V70-3U	10,884	8,999	7,668	6,677	5,911	3,746	2,726	2,141	1,729	1,447	1,242	1,086
SU1000XLa	9 BP24V70-3U	11,649	9,713	8,326	7,283	6,471	4,144	3,031	2,388	1,934	1,622	1,394	1,221
SU1000XLa	10 BP24V70-3U	12,344	10,372	8,940	7,854	7,001	4,528	3,328	2,631	2,136	1,794	1,545	1,354

All runtime values are in minutes.