



SU1000XLCD Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			20	40	60	80	100	150	200	300	400	500	600	700	800	900
SU1000XLCD	Internal batteries	0	244	154	110	85	68	45	33	21	15	11	8.1	6.2	4.8	3.8
SU1000XLCD	BP24V15RT2U	1	691	451	330	257	209	139	102	65	46	35	27	22	19	16
SU1000XLCD	BP24V28-2U	1	1,131	751	556	438	359	244	181	116	84	64	50	41	35	30
SU1000XLCD	BP24V70-3U	1	2,373	1,620	1,223	978	812	564	428	283	207	160	129	107	90	78
SU1000XLCD	BP24V70-3U	2	4,198	2,950	2,267	1,837	1,541	1,092	840	568	424	332	270	226	193	168
SU1000XLCD	BP24V70-3U	3	5,772	4,149	3,232	2,642	2,232	1,601	1,242	850	641	507	414	349	300	262
SU1000XLCD	BP24V70-3U	4	7,142	5,233	4,123	3,398	2,887	2,091	1,634	1,128	856	681	559	473	408	358
SU1000XLCD	BP24V70-3U	5	8,345	6,219	4,951	4,108	3,508	2,563	2,013	1,401	1,068	853	703	596	516	454
SU1000XLCD	BP24V70-3U	6	9,410	7,119	5,720	4,777	4,098	3,017	2,382	1,668	1,277	1,024	846	719	624	550
SU1000XLCD	BP24V70-3U	7	10,360	7,944	6,437	5,408	4,659	3,455	2,740	1,930	1,483	1,192	988	842	731	645
SU1000XLCD	BP24V70-3U	8	11,212	8,704	7,108	6,003	5,193	3,878	3,088	2,187	1,686	1,359	1,129	963	838	741
SU1000XLCD	BP24V70-3U	9	11,980	9,404	7,736	6,567	5,703	4,285	3,426	2,438	1,886	1,524	1,268	1,084	944	835
SU1000XLCD	BP24V70-3U	10	12,677	10,053	8,325	7,101	6,188	4,678	3,755	2,685	2,083	1,686	1,406	1,203	1,050	930

All runtime values are shown in minutes.