



SU100KX2 Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in Watts													
			5,900	11,600	17,300	23,000	28,700	34,400	40,100	45,800	51,500	57,200	62,900	68,600	74,300	80,000
SU100KX2	BP480V40C	2	282	134	87	63	49	38	32	27	23	20	18	16	14	13
SU100KX2	BP480V200	1	183	85	55	39	30	24	20	16	14	12	11	9.5	8.4	7.6
SU100KX2	BP480V200	2	402	195	128	93	72	57	48	41	35	30	27	24	21	20
SU100KX2	BP480V200	3	622	309	207	152	119	95	79	68	58	51	45	40	36	33
SU100KX2	BP480V200	4	840	425	287	213	167	134	113	97	83	73	65	58	52	48
SU100KX2	BP480V300	1	274	130	85	61	47	37	31	26	22	19	17	15	14	12
SU100KX2	BP480V300	2	586	291	194	142	111	89	74	63	54	48	42	38	34	31
SU100KX2	BP480V300	3	895	455	307	229	180	144	122	104	89	79	70	63	57	52
SU100KX2	BP480V300	4	1198	619	423	316	251	202	171	147	127	112	99	90	81	74
SU100KX2	BP480V400	1	374	181	118	86	67	53	44	37	32	28	25	22	20	18
SU100KX2	BP480V400	2	784	396	266	197	155	124	104	89	77	67	60	54	48	44
SU100KX2	BP480V400	3	1186	613	418	313	248	200	169	145	125	111	98	89	80	73
SU100KX2	BP480V400	4	1577	828	570	430	342	278	236	204	176	156	139	126	114	104
SU100KX2	BP480V500	1	522	257	171	125	97	78	65	55	47	41	37	33	29	27
SU100KX2	BP480V500	2	1074	552	375	280	221	178	151	129	111	98	87	79	71	65
SU100KX2	BP480V500	3	1607	844	582	439	350	284	241	208	180	160	142	129	116	107
SU100KX2	BP480V500	4	2119	1132	787	598	479	391	334	289	251	224	199	181	164	151

All runtime values are shown in minutes.