



SU10KRT3UHV Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			1,200	1,800	2,400	3,000	3,600	4,200	4,800	5,400	6,000	6,600	7,200	7,800	8,400	9,000
SU10KRT3UHV	INCLUDED BATTERIES	0	62	39	27	21	17	14	11	9.6	8.2	7.1	6.2	5.5	4.9	4.3
SU10KRT3UHV	BP240V10RT3U	1	143	90	64	49	39	32	27	23	20	18	16	14	13	12
SU10KRT3UHV	BP240V10RT3U	2	229	146	105	81	65	54	45	39	34	30	27	24	22	20
SU10KRT3UHV	BP240V10RT3U	3	318	205	148	114	92	77	65	56	49	44	39	35	32	29
SU10KRT3UHV	BP240V10RT3U	4	406	265	193	149	121	101	86	74	65	58	52	47	43	39
SU10KRT3UHV	BP240V10RT3U	5	495	325	238	185	150	126	107	93	81	72	65	59	54	49
SU10KRT3UHV	BP240V10RT3U	6	584	386	283	221	180	151	129	112	98	88	79	71	65	60
SU10KRT3UHV	BP240V10RT3U	7	673	446	329	258	210	176	151	131	116	103	93	84	77	70
SU10KRT3UHV	BP240V10RT3U	8	761	507	375	295	241	202	173	151	133	119	107	97	89	81
SU10KRT3UHV	BP240V10RT3U	9	849	567	421	331	271	228	196	171	151	135	122	110	101	93
SU10KRT3UHV	BP240V10RT3U	10	936	628	467	368	302	255	219	191	169	151	136	124	113	104
SU10KRT3UHV	BP240V787C-1PH	1	732	487	360	282	231	194	166	144	127	114	102	93	85	78
SU10KRT3UHV	BP240V787C-1PH	2	1,477	1,006	756	602	498	423	366	321	285	256	232	211	194	179
SU10KRT3UHV	BP240V787C-1PH	3	2,183	1,508	1,145	919	765	653	568	500	446	402	366	335	308	285
SU10KRT3UHV	BP240V787C-1PH	4	2,852	1,992	1,524	1,229	1,028	881	768	679	608	549	500	459	423	393
SU10KRT3UHV	BP240V787C-1PH	5	3,486	2,458	1,892	1,533	1,286	1,105	967	857	768	695	635	583	539	500

All runtime values are shown in minutes.