



## SU12000RT4U Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			600	1,200	1,800	2,400	3,000	3,600	4,200	4,800	5,400	6,000	6,600	7,200	7,800	8,400
SU12000RT4U	INCLUDED BATTERIES	0	211	104	64	44	33	25	20	17	14	12	10	9.0	7.9	7.0
SU12000RT4U	BP192V18-4U	1	472	249	164	119	93	75	62	53	46	40	36	32	29	26
SU12000RT4U	BP192V18-4U	2	726	392	262	193	151	123	103	88	76	67	60	54	49	45
SU12000RT4U	BP192V18-4U	3	977	536	361	268	211	173	145	125	109	96	86	77	70	64
SU12000RT4U	BP192V18-4U	4	1,224	679	461	345	273	224	189	162	142	126	112	101	92	84
SU12000RT4U	BP192V18-4U	5	1,466	821	561	421	334	275	233	201	176	156	140	126	115	105
SU12000RT4U	BP192V18-4U	6	1,704	962	661	498	396	327	277	240	210	187	168	152	138	127
SU12000RT4U	BP192V18-4U	7	1,938	1,101	760	574	459	379	322	279	245	218	196	178	162	149
SU12000RT4U	BP192V18-4U	8	2,168	1,240	858	651	521	432	367	318	280	250	225	204	186	171
SU12000RT4U	BP192V18-4U	9	2,394	1,377	956	727	583	484	412	358	316	281	253	230	210	193
SU12000RT4U	BP192V18-4U	10	2,615	1,512	1,053	802	645	536	457	398	351	313	282	256	235	216

All runtime values are shown in minutes.