



SU12KRT4UHW Estimated Runtime

Load in Watts

UPS	Battery Pack	BP Qty.	1000W	2000W	3000W	4000W	5000W	6000W	7000W	8000W	9000W	10,000W	10,800W
SU12KRT4UHW	Internal Batteries	0	65	29	18	12	9.1	7.0	5.6	4.5	3.8	2.8	2.0
SU12KRT4UHW	BP192V12-3U	2	277	133	84	59	46	36	30	25	21	18	17
SU12KRT4UHW	BP192V12-3U	4	501	248	160	115	89	71	58	49	42	37	34
SU12KRT4UHW	BP192V12-3U	6	721	364	239	173	135	108	89	76	65	57	53
SU12KRT4UHW	BP192V12-3U	8	941	482	319	233	183	147	122	104	90	79	73
SU12KRT4UHW	BP192V12-3U	10	1156	600	400	293	231	187	156	133	115	101	94
SU12KRT4UHW	BP192V12-3U	12	1370	717	481	354	280	227	190	162	141	124	115
SU12KRT4UHW	BP192V12-3U	14	1579	834	562	415	330	268	225	192	167	147	137
SU12KRT4UHW	BP192V12-3U	16	1785	949	642	476	379	309	259	222	194	171	159
SU12KRT4UHW	BP192V12-3U	18	1989	1064	723	538	429	351	294	253	221	195	182
SU12KRT4UHW	BP192V12-3U	20	2188	1178	802	598	478	392	330	283	247	219	204
SU12KRT4UHW	BP192V557C-1PH	2	977	502	332	243	191	154	128	109	94	82	77
SU12KRT4UHW	BP192V557C-1PH	4	1938	1036	703	522	416	340	286	245	214	189	176
SU12KRT4UHW	BP192V997C-1PH	2	1562	824	555	410	326	265	222	190	165	145	135
SU12KRT4UHW	BP192V997C-1PH	4	3004	1652	1138	856	689	567	480	414	363	323	302
SU12KRT4UHW	BP192V1207C-1PH	2	1820	969	656	487	387	316	265	227	198	175	163
SU12KRT4UHW	BP192V1207C-1PH	4	3459	1923	1332	1006	811	670	568	491	432	384	360
SU12KRT4UHW	BP192V1507C-1PH	2	2434	1319	902	675	540	443	374	322	282	250	233
SU12KRT4UHW	BP192V1507C-1PH	4	4511	2568	1798	1368	1110	921	784	681	601	536	503
SU12KRT4UHW	BP192V1507C-1PH	6	6263	3701	2637	2029	1659	1386	1186	1035	917	822	772
SU12KRT4UHW	BP192V1507C-1PH	8	7762	4734	3422	2657	2185	1835	1577	1381	1227	1102	1037

All runtime values are in minutes.