



SU1500RTLCD2U Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			20	50	100	200	300	400	500	600	700	800	900	1,000	1,200	1,350
SU1500RTLCD2U	Internal batteries	0	345	199	112	56	36	26	20	16	13	11	8.8	7.4	5.3	4.2
SU1500RTLCD2U	BP48V24-2U	1	1,284	781	461	242	159	116	90	72	60	51	44	38	30	26
SU1500RTLCD2U	BP48V27-2US	1	1,733	1,068	639	342	226	166	130	105	88	74	64	56	45	38
SU1500RTLCD2U	BP48V27-2US	2	2,991	1,895	1,163	641	434	324	255	209	176	150	131	115	92	80
SU1500RTLCD2U	BP48V27-2US	3	4,131	2,673	1,669	937	642	483	384	317	268	230	201	178	143	125
SU1500RTLCD2U	BP48V27-2US	4	5,167	3,404	2,156	1,228	848	642	514	426	361	311	273	242	196	171
SU1500RTLCD2U	BP48V27-2US	5	6,113	4,092	2,625	1,512	1,052	801	643	534	455	393	345	307	250	218
SU1500RTLCD2U	BP48V27-2US	6	6,981	4,741	3,076	1,791	1,253	957	771	643	549	475	418	372	304	266
SU1500RTLCD2U	BP48V27-2US	7	7,778	5,354	3,511	2,063	1,451	1,112	898	751	642	557	491	438	359	315
SU1500RTLCD2U	BP48V27-2US	8	8,515	5,935	3,931	2,330	1,646	1,266	1,025	858	735	639	564	504	413	363
SU1500RTLCD2U	BP48V27-2US	9	9,197	6,485	4,336	2,592	1,838	1,418	1,150	965	827	720	636	569	468	412
SU1500RTLCD2U	BP48V27-2US	10	9,830	7,006	4,727	2,848	2,027	1,568	1,274	1,070	919	801	709	634	523	460
SU1500RTLCD2U	BP48V60RT-3U	1	2,503	1,571	956	521	351	260	204	167	140	119	103	91	73	63
SU1500RTLCD2U	BP48V60RT-3U	2	4,346	2,822	1,768	996	683	515	410	339	287	246	215	191	154	134
SU1500RTLCD2U	BP48V60RT-3U	3	5,931	3,957	2,532	1,456	1,011	769	617	513	436	377	331	294	239	209
SU1500RTLCD2U	BP48V60RT-3U	4	7,308	4,991	3,252	1,901	1,332	1,020	822	686	586	508	447	399	326	286
SU1500RTLCD2U	BP48V60RT-3U	5	8,515	5,935	3,931	2,330	1,646	1,266	1,025	858	735	639	564	504	413	363
SU1500RTLCD2U	BP48V60RT-3U	6	9,582	6,801	4,572	2,746	1,952	1,508	1,225	1,028	883	769	680	608	501	441
SU1500RTLCD2U	BP48V60RT-3U	7	10,533	7,599	5,178	3,148	2,251	1,746	1,422	1,196	1,029	898	795	713	588	519
SU1500RTLCD2U	BP48V60RT-3U	8	11,384	8,335	5,752	3,537	2,543	1,979	1,616	1,363	1,174	1,026	910	816	675	596
SU1500RTLCD2U	BP48V60RT-3U	9	12,151	9,018	6,297	3,913	2,828	2,208	1,807	1,527	1,317	1,153	1,024	919	762	673
SU1500RTLCD2U	BP48V60RT-3U	10	12,847	9,652	6,815	4,277	3,107	2,433	1,996	1,689	1,459	1,279	1,137	1,022	848	751

All runtime values are shown in minutes.