



SU1500RTLCD2UTAA Estimated Runtime

| UPS | Extended Battery Module | EBM QTY | CONNECTED EQUIPMENT LOAD IN WATTS | | | | | | | | | | | | | |
|------------------|-------------------------|---------|-----------------------------------|-----|-----|-----|-----|-----|-----|-----|-------|-------|-------|-------|-------|-------|
| | | | 200 | 300 | 400 | 500 | 600 | 700 | 800 | 900 | 1,000 | 1,100 | 1,200 | 1,250 | 1,300 | 1,350 |
| SU1500RTLCD2UTAA | Internal batteries | 0 | 64 | 42 | 31 | 24 | 19 | 16 | 13 | 11 | 10 | 8 | 7.1 | 6.6 | 6.2 | 5.8 |
| SU1500RTLCD2UTAA | BP48RT2UTAA | 1 | 239 | 157 | 115 | 89 | 72 | 60 | 51 | 44 | 39 | 34 | 31.0 | 29.5 | 28.0 | 27.0 |
| SU1500RTLCD2UTAA | BP48RT2UTAA | 2 | 440 | 290 | 212 | 164 | 133 | 111 | 95 | 82 | 72 | 64 | 57.0 | 54.0 | 52.0 | 50.0 |
| SU1500RTLCD2UTAA | BP48RT2UTAA | 3 | 656 | 432 | 315 | 245 | 199 | 166 | 141 | 122 | 107 | 95 | 86.0 | 81.0 | 78.0 | 74.0 |
| SU1500RTLCD2UTAA | BP48RT2UTAA | 4 | 886 | 583 | 426 | 331 | 268 | 224 | 191 | 165 | 145 | 129 | 116.0 | 110.0 | 105.0 | 100.0 |

All runtime values are shown in minutes.