



SU1500RTXLCDN Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	300	400	500	600	700	800	900	1,000	1,100	1,200	1,300	1,350
SU1500RTXLCDN	Internal batteries	n/a	112	56	36	26	20	16	13	11	8.8	7.4	6.2	5.3	4.5	4.2
SU1500RTXLCDN	BP48V24-2U	1	461	242	159	116	90	72	60	51	44	38	34	30	27	26
SU1500RTXLCDN	BP48V27-2US	1	639	342	226	166	130	105	88	74	64	56	50	45	40	38
SU1500RTXLCDN	BP48V27-2US	2	1,163	641	434	324	255	209	176	150	131	115	103	92	84	80
SU1500RTXLCDN	BP48V27-2US	3	1,669	937	642	483	384	317	268	230	201	178	159	143	130	125
SU1500RTXLCDN	BP48V27-2US	4	2,156	1,228	848	642	514	426	361	311	273	242	217	196	179	171
SU1500RTXLCDN	BP48V27-2US	5	2,625	1,512	1,052	801	643	534	455	393	345	307	276	250	228	218
SU1500RTXLCDN	BP48V27-2US	6	3,076	1,791	1,253	957	771	643	549	475	418	372	335	304	278	266
SU1500RTXLCDN	BP48V27-2US	7	3,511	2,063	1,451	1,112	898	751	642	557	491	438	395	359	328	315
SU1500RTXLCDN	BP48V27-2US	8	3,931	2,330	1,646	1,266	1,025	858	735	639	564	504	454	413	379	363
SU1500RTXLCDN	BP48V27-2US	9	4,336	2,592	1,838	1,418	1,150	965	827	720	636	569	514	468	429	412
SU1500RTXLCDN	BP48V27-2US	10	4,727	2,848	2,027	1,568	1,274	1,070	919	801	709	634	574	523	479	460
SU1500RTXLCDN	BP48V60RT-3U	1	956	521	351	260	204	167	140	119	103	91	81	73	66	63
SU1500RTXLCDN	BP48V60RT-3U	2	1,768	996	683	515	410	339	287	246	215	191	170	154	140	134
SU1500RTXLCDN	BP48V60RT-3U	3	2,532	1,456	1,011	769	617	513	436	377	331	294	264	239	218	209
SU1500RTXLCDN	BP48V60RT-3U	4	3,252	1,901	1,332	1,020	822	686	586	508	447	399	359	326	298	286
SU1500RTXLCDN	BP48V60RT-3U	5	3,931	2,330	1,646	1,266	1,025	858	735	639	564	504	454	413	379	363
SU1500RTXLCDN	BP48V60RT-3U	6	4,572	2,746	1,952	1,508	1,225	1,028	883	769	680	608	550	501	459	441
SU1500RTXLCDN	BP48V60RT-3U	7	5,178	3,148	2,251	1,746	1,422	1,196	1,029	898	795	713	645	588	540	519
SU1500RTXLCDN	BP48V60RT-3U	8	5,752	3,537	2,543	1,979	1,616	1,363	1,174	1,026	910	816	739	675	620	596
SU1500RTXLCDN	BP48V60RT-3U	9	6,297	3,913	2,828	2,208	1,807	1,527	1,317	1,153	1,024	919	834	762	701	673
SU1500RTXLCDN	BP48V60RT-3U	10	6,815	4,277	3,107	2,433	1,996	1,689	1,459	1,279	1,137	1,022	927	848	781	751

All runtime values are shown in minutes.