



## SU1500RTXLCDTAA Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	300	400	500	600	700	800	900	1,000	1,100	1,200	1,300	1,350
SU1500RTXLCDTAA	Internal batteries	n/a	112	56	36	26	20	16	13	11	8.8	7.4	6.2	5.3	4.5	4.2
SU1500RTXLCDTAA	BP48V242UTAA	1	461	242	159	116	90	72	60	51	44	38	34	30	27	26
SU1500RTXLCDTAA	BP48V60RT3UTAA	1	956	521	351	260	204	167	140	119	103	91	81	73	66	63
SU1500RTXLCDTAA	BP48V60RT3UTAA	2	1,768	996	683	515	410	339	287	246	215	191	170	154	140	134
SU1500RTXLCDTAA	BP48V60RT3UTAA	3	2,532	1,456	1,011	769	617	513	436	377	331	294	264	239	218	209
SU1500RTXLCDTAA	BP48V60RT3UTAA	4	3,252	1,901	1,332	1,020	822	686	586	508	447	399	359	326	298	286
SU1500RTXLCDTAA	BP48V60RT3UTAA	5	3,931	2,330	1,646	1,266	1,025	858	735	639	564	504	454	413	379	363
SU1500RTXLCDTAA	BP48V60RT3UTAA	6	4,572	2,746	1,952	1,508	1,225	1,028	883	769	680	608	550	501	459	441
SU1500RTXLCDTAA	BP48V60RT3UTAA	7	5,178	3,148	2,251	1,746	1,422	1,196	1,029	898	795	713	645	588	540	519
SU1500RTXLCDTAA	BP48V60RT3UTAA	8	5,752	3,537	2,543	1,979	1,616	1,363	1,174	1,026	910	816	739	675	620	596
SU1500RTXLCDTAA	BP48V60RT3UTAA	9	6,297	3,913	2,828	2,208	1,807	1,527	1,317	1,153	1,024	919	834	762	701	673
SU1500RTXLCDTAA	BP48V60RT3UTAA	10	6,815	4,277	3,107	2,433	1,996	1,689	1,459	1,279	1,137	1,022	927	848	781	751

All runtime values are shown in minutes.