



SU1500XLCD Estimated Runtime

UPS	Battery Pack	Load in Watts													
		50	100	200	300	400	500	600	700	800	900	1,000	1,100	1,200	1,350
SU1500XLCD	INCLUDED BATTERIES	199	112	56	36	26	20	16	13	11	9.0	7.6	6.5	5.6	4.5
SU1500XLCD	1 BP48V27-2US	1068	639	342	226	166	130	105	88	74	64	56	50	45	38
SU1500XLCD	2 BP48V27-2US	1895	1163	641	434	324	255	209	176	150	131	115	103	92	80
SU1500XLCD	3 BP48V27-2US	2673	1669	937	642	483	384	317	268	230	201	178	159	143	125
SU1500XLCD	4 BP48V27-2US	3404	2156	1228	848	642	514	426	361	311	273	242	217	196	171
SU1500XLCD	5 BP48V27-2US	4092	2625	1512	1052	801	643	534	455	393	345	307	276	250	218
SU1500XLCD	6 BP48V27-2US	4741	3076	1791	1253	957	771	643	549	475	418	372	335	304	266
SU1500XLCD	7 BP48V27-2US	5354	3511	2063	1451	1112	898	751	642	557	491	438	395	359	315
SU1500XLCD	8 BP48V27-2US	5935	3931	2330	1646	1266	1025	858	735	639	564	504	454	413	363
SU1500XLCD	9 BP48V27-2US	6485	4336	2592	1838	1418	1150	965	827	720	636	569	514	468	412
SU1500XLCD	10 BP48V27-2US	7006	4727	2848	2027	1568	1274	1070	919	801	709	634	574	523	460
SU1500XLCD	1 BP48V60RT-3U	1571	956	521	351	260	204	167	140	119	103	91	81	73	63
SU1500XLCD	2 BP48V60RT-3U	2822	1768	996	683	515	410	339	287	246	215	191	170	154	134
SU1500XLCD	3 BP48V60RT-3U	3957	2532	1456	1011	769	617	513	436	377	331	294	264	239	209
SU1500XLCD	4 BP48V60RT-3U	4991	3252	1901	1332	1020	822	686	586	508	447	399	359	326	286
SU1500XLCD	5 BP48V60RT-3U	5935	3931	2330	1646	1266	1025	858	735	639	564	504	454	413	363
SU1500XLCD	6 BP48V60RT-3U	6801	4572	2746	1952	1508	1225	1028	883	769	680	608	550	501	441
SU1500XLCD	7 BP48V60RT-3U	7599	5178	3148	2251	1746	1422	1196	1029	898	795	713	645	588	519
SU1500XLCD	8 BP48V60RT-3U	8335	5752	3537	2543	1979	1616	1363	1174	1026	910	816	739	675	596
SU1500XLCD	9 BP48V60RT-3U	9018	6297	3913	2828	2208	1807	1527	1317	1153	1024	919	834	762	673
SU1500XLCD	10 BP48V60RT-3U	9652	6815	4277	3107	2433	1996	1689	1459	1279	1137	1022	927	848	751

All runtime values are shown in minutes.