



SU16000RT4UHW Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			800	1,600	2,400	3,200	4,000	4,800	5,600	6,400	7,200	8,000	8,800	9,600	10,500	11,200
SU16000RT4UHW	INCLUDED BATTERIES	0	155	72	43	29	21	16	12	10	8.7	7.7	6.8	6.1	5.4	5.0
SU16000RT4UHW	BP192V18-4U	1	356	179	115	83	64	51	42	36	31	27	24	21	19	17
SU16000RT4UHW	BP192V18-4U	2	553	286	186	135	105	84	70	59	51	45	40	36	32	29
SU16000RT4UHW	BP192V18-4U	3	749	393	259	190	148	120	100	85	73	64	57	51	46	42
SU16000RT4UHW	BP192V18-4U	4	943	501	333	245	192	156	131	111	97	85	76	68	61	56
SU16000RT4UHW	BP192V18-4U	5	1,135	609	407	302	237	193	162	139	121	106	95	85	76	70
SU16000RT4UHW	BP192V18-4U	6	1,324	716	482	358	282	231	195	166	145	128	114	103	92	85
SU16000RT4UHW	BP192V18-4U	7	1,511	823	556	415	328	269	227	195	170	150	134	121	108	100
SU16000RT4UHW	BP192V18-4U	8	1,694	929	630	471	373	307	260	223	195	172	154	139	125	115
SU16000RT4UHW	BP192V18-4U	9	1,876	1,034	704	528	419	346	292	251	220	195	174	157	141	131
SU16000RT4UHW	BP192V18-4U	10	2,055	1,139	777	585	465	384	325	280	245	217	195	176	158	147

All runtime values are shown in minutes.