



## SU16KRT-1TFTAA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			1,000	2,000	3,000	4,000	5,000	6,000	7,000	8,000	9,000	10,000	11,000	12,000	13,000	14,000
SU16KRT-1TFTAA	Included Batteries	0	165	76	46	32	23	18	14	12	10	8.9	7.8	7.0	6.3	5.7
SU16KRT-1TFTAA	BP240V10RT3UTAA	2	372	184	118	84	65	52	43	36	31	27	24	21	19	17
SU16KRT-1TFTAA	BP240V10RT3UTAA	4	577	293	190	138	106	86	71	60	52	46	40	36	33	30
SU16KRT-1TFTAA	BP240V10RT3UTAA	6	780	404	264	193	150	121	101	86	74	65	58	52	47	43
SU16KRT-1TFTAA	BP240V10RT3UTAA	8	982	514	340	249	195	158	133	113	98	86	77	69	62	57
SU16KRT-1TFTAA	BP240V10RT3UTAA	10	1181	624	415	307	240	196	164	141	122	108	96	86	78	71
SU16KRT-1TFTAA	BP240V10RT3UTAA	12	1376	734	491	364	286	234	197	169	147	129	115	104	94	86
SU16KRT-1TFTAA	BP240V10RT3UTAA	14	1570	843	566	421	332	273	230	197	172	152	136	122	111	101
SU16KRT-1TFTAA	BP240V10RT3UTAA	16	1760	951	642	479	379	311	263	226	197	174	156	141	128	117
SU16KRT-1TFTAA	BP240V10RT3UTAA	18	1947	1059	717	536	425	350	296	255	223	197	176	159	145	133
SU16KRT-1TFTAA	BP240V10RT3UTAA	20	2132	1166	792	594	471	389	329	284	248	220	197	178	162	149
SU16KRT-1TFTAA	BP240V787C-1PH	2	1697	915	617	460	363	298	252	216	189	167	149	134	122	112
SU16KRT-1TFTAA	BP240V787C-1PH	4	3243	1823	1257	953	764	634	541	469	412	367	330	300	274	252

All runtime values are shown in minutes.