



SU16KRTHW Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2kW	3kW	4kW	5kW	6kW	7kW	8kW	9kW	10kW	11kW	12kW	13kW	14kW	14.4kW
SU16KRTHW	INCLUDED BATTERIES	0	76	46	32	23	18	14	12	10	8.9	7.8	7.0	6.3	5.7	5.5
SU16KRTHW	BP240V10RT3U	2	184	118	84	65	52	43	36	31	27	24	21	19	17	17
SU16KRTHW	BP240V10RT3U	4	293	190	138	106	86	71	60	52	46	40	36	33	30	29
SU16KRTHW	BP240V10RT3U	6	404	264	193	150	121	101	86	74	65	58	52	47	43	41
SU16KRTHW	BP240V10RT3U	8	514	340	249	195	158	133	113	98	86	77	69	62	57	55
SU16KRTHW	BP240V10RT3U	10	624	415	307	240	196	164	141	122	108	96	86	78	71	69
SU16KRTHW	BP240V10RT3U	12	734	491	364	286	234	197	169	147	129	115	104	94	86	83
SU16KRTHW	BP240V10RT3U	14	843	566	421	332	273	230	197	172	152	136	122	111	101	98
SU16KRTHW	BP240V10RT3U	16	951	642	479	379	311	263	226	197	174	156	141	128	117	113
SU16KRTHW	BP240V10RT3U	18	1,059	717	536	425	350	296	255	223	197	176	159	145	133	128
SU16KRTHW	BP240V10RT3U	20	1,166	792	594	471	389	329	284	248	220	197	178	162	149	144
SU16KRTHW	BP240V787C-1PH	2	915	617	460	363	298	252	216	189	167	149	134	122	112	108
SU16KRTHW	BP240V787C-1PH	4	1,823	1,257	953	764	634	541	469	412	367	330	300	274	252	244

All runtime values are shown in minutes.