



## SU2000RTXLCD2U Estimated Runtime

| UPS            | External Battery Pack | BP QTY | CONNECTED EQUIPMENT LOAD IN WATTS |       |       |       |       |       |       |       |       |       |       |       |       |       |
|----------------|-----------------------|--------|-----------------------------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
|                |                       |        | 100                               | 200   | 300   | 400   | 500   | 600   | 700   | 800   | 900   | 1,000 | 1,200 | 1,400 | 1,600 | 1,800 |
| SU2000RTXLCD2U | Internal batteries    | n/a    | 142                               | 72    | 47    | 34    | 26    | 21    | 18    | 15    | 13    | 11    | 8.6   | 6.7   | 5.3   | 4.3   |
| SU2000RTXLCD2U | BP48V24-2U            | 1      | 486                               | 258   | 170   | 124   | 96    | 78    | 65    | 55    | 48    | 42    | 33    | 27    | 23    | 19    |
| SU2000RTXLCD2U | BP48V27-2US           | 1      | 660                               | 356   | 237   | 174   | 136   | 110   | 92    | 79    | 68    | 60    | 48    | 39    | 33    | 28    |
| SU2000RTXLCD2U | BP48V27-2US           | 2      | 1,174                             | 651   | 442   | 330   | 261   | 214   | 180   | 155   | 135   | 119   | 96    | 79    | 67    | 58    |
| SU2000RTXLCD2U | BP48V27-2US           | 3      | 1,669                             | 942   | 647   | 488   | 388   | 320   | 271   | 235   | 206   | 182   | 147   | 122   | 104   | 90    |
| SU2000RTXLCD2U | BP48V27-2US           | 4      | 2,146                             | 1,228 | 850   | 645   | 516   | 428   | 364   | 316   | 278   | 246   | 200   | 167   | 143   | 124   |
| SU2000RTXLCD2U | BP48V27-2US           | 5      | 2,606                             | 1,509 | 1,051 | 801   | 644   | 536   | 457   | 397   | 350   | 311   | 254   | 213   | 182   | 159   |
| SU2000RTXLCD2U | BP48V27-2US           | 6      | 3,050                             | 1,783 | 1,250 | 956   | 771   | 643   | 550   | 479   | 423   | 377   | 308   | 259   | 222   | 194   |
| SU2000RTXLCD2U | BP48V27-2US           | 7      | 3,477                             | 2,052 | 1,445 | 1,109 | 897   | 750   | 642   | 560   | 496   | 443   | 362   | 305   | 263   | 230   |
| SU2000RTXLCD2U | BP48V27-2US           | 8      | 3,890                             | 2,315 | 1,638 | 1,261 | 1,022 | 856   | 734   | 642   | 569   | 508   | 417   | 352   | 303   | 266   |
| SU2000RTXLCD2U | BP48V27-2US           | 9      | 4,288                             | 2,573 | 1,828 | 1,411 | 1,145 | 961   | 826   | 723   | 641   | 574   | 472   | 399   | 344   | 302   |
| SU2000RTXLCD2U | BP48V27-2US           | 10     | 4,673                             | 2,826 | 2,015 | 1,560 | 1,268 | 1,066 | 917   | 804   | 714   | 639   | 526   | 446   | 385   | 338   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 1      | 970                               | 533   | 359   | 267   | 210   | 172   | 144   | 124   | 108   | 95    | 76    | 63    | 53    | 46    |
| SU2000RTXLCD2U | BP48V60RT-3U          | 2      | 1,766                             | 1,000 | 688   | 519   | 414   | 342   | 290   | 251   | 220   | 195   | 157   | 131   | 112   | 97    |
| SU2000RTXLCD2U | BP48V60RT-3U          | 3      | 2,516                             | 1,453 | 1,011 | 770   | 618   | 514   | 438   | 381   | 336   | 298   | 243   | 203   | 174   | 152   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 4      | 3,223                             | 1,892 | 1,328 | 1,018 | 821   | 686   | 587   | 511   | 452   | 403   | 330   | 277   | 238   | 208   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 5      | 3,890                             | 2,315 | 1,638 | 1,261 | 1,022 | 856   | 734   | 642   | 569   | 508   | 417   | 352   | 303   | 266   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 6      | 4,521                             | 2,725 | 1,940 | 1,501 | 1,219 | 1,024 | 881   | 771   | 685   | 613   | 504   | 427   | 369   | 324   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 7      | 5,118                             | 3,122 | 2,236 | 1,736 | 1,414 | 1,191 | 1,026 | 900   | 800   | 717   | 592   | 502   | 434   | 382   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 8      | 5,684                             | 3,506 | 2,525 | 1,967 | 1,607 | 1,355 | 1,170 | 1,027 | 915   | 821   | 679   | 577   | 500   | 440   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 9      | 6,222                             | 3,878 | 2,807 | 2,193 | 1,796 | 1,518 | 1,312 | 1,154 | 1,029 | 924   | 765   | 651   | 565   | 498   |
| SU2000RTXLCD2U | BP48V60RT-3U          | 10     | 6,733                             | 4,238 | 3,082 | 2,416 | 1,983 | 1,678 | 1,453 | 1,279 | 1,142 | 1,026 | 852   | 726   | 631   | 557   |

All runtime values are shown in minutes.