



SU20KRT-1TF Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2kW	4kW	6kW	8kW	9kW	10kW	11kW	12kW	13kW	14kW	15kW	16kW	17kW	18kW
SU20KRT-1TF	INCLUDED BATTERIES	0	78	35	22	16	14	12	10	8.7	7.6	6.7	6.0	5.4	4.8	4.3
SU20KRT-1TF	BP240V10RT3U	2	175	79	49	34	29	26	23	20	18	16	15	14	13	12
SU20KRT-1TF	BP240V10RT3U	4	278	130	81	57	49	43	38	34	31	28	26	23	22	20
SU20KRT-1TF	BP240V10RT3U	6	383	182	114	81	70	62	55	49	44	40	37	34	31	29
SU20KRT-1TF	BP240V10RT3U	8	489	236	149	107	93	81	72	65	59	54	49	45	42	39
SU20KRT-1TF	BP240V10RT3U	10	594	290	185	133	116	102	91	81	74	67	62	57	52	49
SU20KRT-1TF	BP240V10RT3U	12	699	345	221	160	139	123	109	98	89	81	75	69	64	60
SU20KRT-1TF	BP240V10RT3U	14	803	400	258	187	163	144	128	116	105	96	88	81	75	70
SU20KRT-1TF	BP240V10RT3U	16	907	454	295	214	187	165	148	133	121	111	102	94	87	81
SU20KRT-1TF	BP240V10RT3U	18	1,010	509	331	241	211	187	167	151	137	126	116	107	99	93
SU20KRT-1TF	BP240V10RT3U	20	1,112	564	368	269	236	209	187	169	154	141	130	120	111	104
SU20KRT-1TF	BP240V787C-1PH	2	873	436	282	205	179	158	141	127	116	106	97	90	83	78
SU20KRT-1TF	BP240V787C-1PH	4	1,743	907	602	445	393	349	314	285	260	239	221	205	190	179

All runtime values are shown in minutes.