



SU20KRT-1TFTAA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			1,000	2,000	4,000	6,000	8,000	10,000	11,000	12,000	13,000	14,000	15,000	16,000	17,000	18,000
SU20KRT-1TFTAA	Included Batteries	0	163	78	35	22	16	12	10	8.7	7.6	6.7	6.0	5.4	4.8	4.3
SU20KRT-1TFTAA	BP240V10RT3UTAA	2	354	175	79	49	34	26	23	20	18	16	15	14	13	12
SU20KRT-1TFTAA	BP240V10RT3UTAA	4	551	278	130	81	57	43	38	34	31	28	26	23	22	20
SU20KRT-1TFTAA	BP240V10RT3UTAA	6	746	383	182	114	81	62	55	49	44	40	37	34	32	29
SU20KRT-1TFTAA	BP240V10RT3UTAA	8	939	489	236	149	107	81	72	65	59	54	49	45	42	39
SU20KRT-1TFTAA	BP240V10RT3UTAA	10	1130	594	290	185	133	102	91	81	74	67	62	57	53	49
SU20KRT-1TFTAA	BP240V10RT3UTAA	12	1319	699	345	221	160	123	109	98	89	81	75	69	64	60
SU20KRT-1TFTAA	BP240V10RT3UTAA	14	1504	803	400	258	187	144	128	116	105	96	88	81	76	70
SU20KRT-1TFTAA	BP240V10RT3UTAA	16	1688	907	454	295	214	165	148	133	121	111	102	94	87	81
SU20KRT-1TFTAA	BP240V10RT3UTAA	18	1868	1010	509	331	241	187	167	151	137	126	116	107	99	93
SU20KRT-1TFTAA	BP240V10RT3UTAA	20	2046	1112	564	368	269	209	187	169	154	141	130	120	112	104
SU20KRT-1TFTAA	BP240V787C-1PH	2	1627	873	436	282	205	158	141	127	116	106	97	90	83	78
SU20KRT-1TFTAA	BP240V787C-1PH	4	3119	1743	907	602	445	349	314	285	260	239	221	205	191	179

All runtime values are shown in minutes.