



SU20KRTAA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			1,000	2,000	4,000	6,000	8,000	10,000	11,000	12,000	13,000	14,000	15,000	16,000	17,000	18,000
SU20KRTAA	Included Batteries	0	163	78	35	22	16	12	10	8.7	7.6	6.7	6.0	5.4	4.8	4.3
SU20KRTAA	BP240V10RT3UTAA	2	354	175	79	49	34	26	23	20	18	16	15	14	13	12
SU20KRTAA	BP240V10RT3UTAA	4	551	278	130	81	57	43	38	34	31	28	26	23	22	20
SU20KRTAA	BP240V10RT3UTAA	6	746	383	182	114	81	62	55	49	44	40	37	34	32	29
SU20KRTAA	BP240V10RT3UTAA	8	939	489	236	149	107	81	72	65	59	54	49	45	42	39
SU20KRTAA	BP240V10RT3UTAA	10	1130	594	290	185	133	102	91	81	74	67	62	57	53	49
SU20KRTAA	BP240V10RT3UTAA	12	1319	699	345	221	160	123	109	98	89	81	75	69	64	60
SU20KRTAA	BP240V10RT3UTAA	14	1504	803	400	258	187	144	128	116	105	96	88	81	76	70
SU20KRTAA	BP240V10RT3UTAA	16	1688	907	454	295	214	165	148	133	121	111	102	94	87	81
SU20KRTAA	BP240V10RT3UTAA	18	1868	1010	509	331	241	187	167	151	137	126	116	107	99	93
SU20KRTAA	BP240V10RT3UTAA	20	2046	1112	564	368	269	209	187	169	154	141	130	120	112	104
SU20KRTAA	BP240V787C-1PH	2	1627	873	436	282	205	158	141	127	116	106	97	90	83	78
SU20KRTAA	BP240V787C-1PH	4	3119	1743	907	602	445	349	314	285	260	239	221	205	191	179

All runtime values are shown in minutes.