



## SU20KRTG Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2kW	4kW	6kW	8kW	9kW	10kW	11kW	12kW	13kW	14kW	15kW	16kW	17kW	18kW
SU20KRTG	INCLUDED BATTERIES	0	78	35	22	16	14	12	10	8.7	7.6	6.7	6.0	5.4	4.8	4.3
SU20KRTG	BP240V10RT3U	2	175	79	49	34	29	26	23	20	18	16	15	14	13	12
SU20KRTG	BP240V10RT3U	4	278	130	81	57	49	43	38	34	31	28	26	23	22	20
SU20KRTG	BP240V10RT3U	6	383	182	114	81	70	62	55	49	44	40	37	34	31	29
SU20KRTG	BP240V10RT3U	8	489	236	149	107	93	81	72	65	59	54	49	45	42	39
SU20KRTG	BP240V10RT3U	10	594	290	185	133	116	102	91	81	74	67	62	57	52	49
SU20KRTG	BP240V10RT3U	12	699	345	221	160	139	123	109	98	89	81	75	69	64	60
SU20KRTG	BP240V10RT3U	14	803	400	258	187	163	144	128	116	105	96	88	81	75	70
SU20KRTG	BP240V10RT3U	16	907	454	295	214	187	165	148	133	121	111	102	94	87	81
SU20KRTG	BP240V10RT3U	18	1,010	509	331	241	211	187	167	151	137	126	116	107	99	93
SU20KRTG	BP240V10RT3U	20	1,112	564	368	269	236	209	187	169	154	141	130	120	111	104
SU20KRTG	BP240V787C-1PH	2	873	436	282	205	179	158	141	127	116	106	97	90	83	78
SU20KRTG	BP240V787C-1PH	4	1,743	907	602	445	393	349	314	285	260	239	221	205	190	179

All runtime values are shown in minutes.