



## SU20KX Estimated Runtime

UPS	Battery Pack qty & model	Load in Watts													
		1,000	2,000	3,000	4,000	5,000	6,000	7,000	8,000	9,000	10,000	11,000	12,000	14,000	16,000
SU20KX	INCLUDED BATTERIES	134	68	43	31	24	19	15	13	11	10	8.9	8.0	6.6	5.5
SU20KX	2 SURBC2030	298	157	102	74	57	46	38	32	29	25	23	21	17	15
SU20KX	1 BP480V26B	581	308	202	147	114	92	76	65	57	51	46	41	34	29
SU20KX	1 BP480V26B + 2 SURBC2030	715	375	245	178	137	111	92	78	68	61	54	49	41	35
SU20KX	1 BP480V40C	842	457	305	224	175	142	119	102	90	80	72	65	55	47
SU20KX	1 BP480V40C +2 SURBC2030	975	524	348	255	199	161	135	115	101	90	81	73	61	52
SU20KX	1 BP480V200	1117	617	416	309	244	199	167	143	127	114	102	93	78	67
SU20KX	1 BP480V300	1531	861	589	442	350	288	243	210	186	167	151	138	117	100
SU20KX	1 BP480V400	1966	1123	775	586	467	386	328	284	253	227	206	188	160	138
SU20KX	1 BP480V500	2584	1501	1047	797	640	532	454	394	352	318	289	265	226	196
SU20KX	2 BP480V300	2842	1662	1163	888	715	595	508	442	396	357	325	298	255	221
SU20KX	2 BP480V400	3614	2151	1520	1169	945	791	678	592	531	481	439	403	346	302
SU20KX	2 BP480V500	4672	2842	2031	1574	1280	1076	926	812	731	664	607	559	482	422
SU20KX	3 BP480V400	5060	3102	2226	1729	1410	1187	1023	897	808	735	673	620	535	469
SU20KX	3 BP480V500	6432	4050	2945	2308	1893	1602	1386	1220	1102	1005	922	852	737	649
SU20KX	4 BP480V500	7935	5142	3795	3001	2478	2107	1831	1617	1465	1338	1231	1139	990	873

*All runtime values are shown in minutes.*