



SU2200RTXL2UN Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	300	500	600	700	800	900	1,000	1,100	1,200	1,300	1,400	1,500	1,600
SU2200RTXL2UN	Internal batteries	0	141	45	25	20	17	14	12	10	8.6	7.4	6.5	5.7	5.1	4.5
SU2200RTXL2UN	BP48V24-2U	1	488	170	97	78	65	55	48	42	37	33	30	27	25	23
SU2200RTXL2UN	BP48V27-2US	1	662	238	137	111	93	79	68	60	53	48	43	39	36	33
SU2200RTXL2UN	BP48V27-2US	2	1,177	443	262	215	181	156	135	119	106	96	87	79	73	67
SU2200RTXL2UN	BP48V27-2US	3	1,674	649	390	322	273	236	206	182	163	147	134	122	112	104
SU2200RTXL2UN	BP48V27-2US	4	2,153	854	518	430	366	317	278	246	221	200	182	167	154	143
SU2200RTXL2UN	BP48V27-2US	5	2,614	1,055	646	538	459	399	350	311	280	254	231	213	196	182
SU2200RTXL2UN	BP48V27-2US	6	3,058	1,254	774	645	552	481	423	377	339	308	281	259	239	222
SU2200RTXL2UN	BP48V27-2US	7	3,487	1,451	900	753	645	563	496	443	399	362	332	305	282	263
SU2200RTXL2UN	BP48V27-2US	8	3,900	1,644	1,025	859	737	644	569	508	458	417	382	352	326	303
SU2200RTXL2UN	BP48V27-2US	9	4,300	1,834	1,150	965	829	726	641	574	518	472	432	399	370	344
SU2200RTXL2UN	BP48V27-2US	10	4,685	2,022	1,273	1,070	921	807	714	639	578	526	483	446	413	385
SU2200RTXL2UN	BP48V60RT-3U	1	973	361	211	173	145	124	108	95	85	76	69	63	58	53
SU2200RTXL2UN	BP48V60RT-3U	2	1,771	690	415	343	291	252	220	195	174	157	143	131	121	112
SU2200RTXL2UN	BP48V60RT-3U	3	2,523	1,015	621	516	440	382	336	298	268	243	222	203	188	174
SU2200RTXL2UN	BP48V60RT-3U	4	3,232	1,333	824	688	589	514	452	403	363	330	301	277	256	238
SU2200RTXL2UN	BP48V60RT-3U	5	3,900	1,644	1,025	859	737	644	569	508	458	417	382	352	326	303
SU2200RTXL2UN	BP48V60RT-3U	6	4,533	1,947	1,224	1,028	884	774	685	613	554	504	463	427	396	369
SU2200RTXL2UN	BP48V60RT-3U	7	5,131	2,244	1,420	1,195	1,030	904	800	717	649	592	543	502	466	434
SU2200RTXL2UN	BP48V60RT-3U	8	5,698	2,533	1,613	1,360	1,174	1,032	915	821	743	679	624	577	536	500
SU2200RTXL2UN	BP48V60RT-3U	9	6,237	2,816	1,803	1,524	1,317	1,159	1,029	924	838	765	704	651	606	565
SU2200RTXL2UN	BP48V60RT-3U	10	6,749	3,093	1,990	1,685	1,459	1,284	1,142	1,026	931	852	784	726	675	631

All runtime values are shown in minutes.