



SU2200RTXLCD2U Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	400	600	800	1,000	1,100	1,200	1,300	1,400	1,500	1,600	1,700	1,800
SU2200RTXLCD2U	Internal batteries	0	141	70	32	20	14	10	8.9	7.8	6.9	6.1	5.5	4.9	4.4	4.0
SU2200RTXLCD2U	BP48V24-2U	1	486	258	124	78	55	42	37	33	30	27	25	23	21	19
SU2200RTXLCD2U	BP48V27-2US	1	660	356	174	110	79	60	53	48	43	39	36	33	31	28
SU2200RTXLCD2U	BP48V27-2US	2	1,174	651	330	214	155	119	106	96	87	79	73	67	62	58
SU2200RTXLCD2U	BP48V27-2US	3	1,669	942	488	320	235	182	163	147	134	122	112	104	97	90
SU2200RTXLCD2U	BP48V27-2US	4	2,146	1,228	645	428	316	246	221	200	182	167	154	143	133	124
SU2200RTXLCD2U	BP48V27-2US	5	2,606	1,509	801	536	397	311	280	254	231	213	196	182	170	159
SU2200RTXLCD2U	BP48V27-2US	6	3,050	1,783	956	643	479	377	339	308	281	259	239	222	207	194
SU2200RTXLCD2U	BP48V27-2US	7	3,477	2,052	1,109	750	560	443	399	362	332	305	282	263	245	230
SU2200RTXLCD2U	BP48V27-2US	8	3,890	2,315	1,261	856	642	508	458	417	382	352	326	303	283	266
SU2200RTXLCD2U	BP48V27-2US	9	4,288	2,573	1,411	961	723	574	518	472	432	399	370	344	322	302
SU2200RTXLCD2U	BP48V27-2US	10	4,673	2,826	1,560	1,066	804	639	578	526	483	446	413	385	360	338
SU2200RTXLCD2U	BP48V60RT-3U	1	970	533	267	172	124	95	85	76	69	63	58	53	49	46
SU2200RTXLCD2U	BP48V60RT-3U	2	1,766	1,000	519	342	251	195	174	157	143	131	121	112	104	97
SU2200RTXLCD2U	BP48V60RT-3U	3	2,516	1,453	770	514	381	298	268	243	222	203	188	174	162	152
SU2200RTXLCD2U	BP48V60RT-3U	4	3,223	1,892	1,018	686	511	403	363	330	301	277	256	238	222	208
SU2200RTXLCD2U	BP48V60RT-3U	5	3,890	2,315	1,261	856	642	508	458	417	382	352	326	303	283	266
SU2200RTXLCD2U	BP48V60RT-3U	6	4,521	2,725	1,501	1,024	771	613	554	504	463	427	396	369	345	324
SU2200RTXLCD2U	BP48V60RT-3U	7	5,118	3,122	1,736	1,191	900	717	649	592	543	502	466	434	407	382
SU2200RTXLCD2U	BP48V60RT-3U	8	5,684	3,506	1,967	1,355	1,027	821	743	679	624	577	536	500	468	440
SU2200RTXLCD2U	BP48V60RT-3U	9	6,222	3,878	2,193	1,518	1,154	924	838	765	704	651	606	565	530	498
SU2200RTXLCD2U	BP48V60RT-3U	10	6,733	4,238	2,416	1,678	1,279	1,026	931	852	784	726	675	631	592	557

All runtime values are shown in minutes.