



## SU2200XLA Estimated Runtime

UPS	Battery Pack	Load in Watts													
		50	100	200	300	400	500	600	700	800	900	1,000	1,200	1,400	1,600
SU2200XLA	INCLUDED BATTERIES	249	141	71	45	32	25	20	17	14	12	10	7.4	5.7	4.5
SU2200XLA	1 BP48V27-2US	1097	662	357	238	175	137	111	93	79	68	60	48	39	33
SU2200XLA	2 BP48V27-2US	1902	1177	653	443	331	262	215	181	156	135	119	96	79	67
SU2200XLA	3 BP48V27-2US	2661	1674	946	649	490	390	322	273	236	206	182	147	122	104
SU2200XLA	4 BP48V27-2US	3374	2153	1233	854	647	518	430	366	317	278	246	200	167	143
SU2200XLA	5 BP48V27-2US	4048	2614	1514	1055	804	646	538	459	399	350	311	254	213	182
SU2200XLA	6 BP48V27-2US	4684	3058	1789	1254	960	774	645	552	481	423	377	308	259	222
SU2200XLA	7 BP48V27-2US	5285	3487	2059	1451	1114	900	753	645	563	496	443	362	305	263
SU2200XLA	8 BP48V27-2US	5855	3900	2323	1644	1266	1025	859	737	644	569	508	417	352	303
SU2200XLA	9 BP48V27-2US	6396	4300	2582	1834	1417	1150	965	829	726	641	574	472	399	344
SU2200XLA	10 BP48V27-2US	6909	4685	2835	2022	1565	1273	1070	921	807	714	639	526	446	385
SU2200XLA	1 BP48V60RT-3U	1586	973	535	361	268	211	173	145	124	108	95	76	63	53
SU2200XLA	2 BP48V60RT-3U	2807	1771	1003	690	521	415	343	291	252	220	195	157	131	112
SU2200XLA	3 BP48V60RT-3U	3916	2523	1458	1015	773	621	516	440	382	336	298	243	203	174
SU2200XLA	4 BP48V60RT-3U	4928	3232	1898	1333	1022	824	688	589	514	452	403	330	277	238
SU2200XLA	5 BP48V60RT-3U	5855	3900	2323	1644	1266	1025	859	737	644	569	508	417	352	303
SU2200XLA	6 BP48V60RT-3U	6707	4533	2734	1947	1506	1224	1028	884	774	685	613	504	427	369
SU2200XLA	7 BP48V60RT-3U	7493	5131	3132	2244	1742	1420	1195	1030	904	800	717	592	502	434
SU2200XLA	8 BP48V60RT-3U	8220	5698	3517	2533	1974	1613	1360	1174	1032	915	821	679	577	500
SU2200XLA	9 BP48V60RT-3U	8894	6237	3890	2816	2201	1803	1524	1317	1159	1029	924	765	651	565
SU2200XLA	10 BP48V60RT-3U	9521	6749	4251	3093	2425	1990	1685	1459	1284	1142	1026	852	726	631

All runtime values are shown in minutes.