



SU2200XLCD Estimated Runtime

UPS	Battery Pack	Load in Watts													
		50	100	200	300	400	500	600	700	800	1,000	1,200	1,400	1,600	1,800
SU2200XLCD	INCLUDED BATTERIES	257	147	74	48	34	26	21	18	15	11	8.5	6.7	5.4	4.5
SU2200XLCD	1 BP48V27-2US	1127	686	372	249	183	143	117	98	83	63	50	41	34	29
SU2200XLCD	2 BP48V27-2US	1953	1217	680	463	346	274	225	190	164	125	100	82	69	60
SU2200XLCD	3 BP48V27-2US	2728	1729	983	677	511	408	337	286	247	191	153	127	107	93
SU2200XLCD	4 BP48V27-2US	3457	2222	1280	889	676	541	450	383	332	258	208	173	147	127
SU2200XLCD	5 BP48V27-2US	4143	2696	1571	1098	839	675	562	480	418	326	264	220	188	163
SU2200XLCD	6 BP48V27-2US	4791	3152	1856	1305	1000	807	674	577	503	394	320	268	229	199
SU2200XLCD	7 BP48V27-2US	5403	3592	2134	1508	1160	939	786	674	588	463	376	316	270	236
SU2200XLCD	8 BP48V27-2US	5982	4015	2407	1708	1318	1069	897	770	673	531	433	364	312	273
SU2200XLCD	9 BP48V27-2US	6530	4424	2673	1905	1474	1198	1007	866	758	599	490	412	354	310
SU2200XLCD	10 BP48V27-2US	7051	4818	2934	2099	1628	1326	1116	961	843	667	546	460	396	347
SU2200XLCD	1 BP48V60RT-3U	1629	1007	557	377	281	221	181	152	131	100	79	65	55	47
SU2200XLCD	2 BP48V60RT-3U	2877	1829	1043	720	544	434	359	305	264	204	164	136	115	100
SU2200XLCD	3 BP48V60RT-3U	4009	2602	1513	1057	806	648	540	460	400	313	253	210	179	156
SU2200XLCD	4 BP48V60RT-3U	5040	3330	1968	1386	1064	860	719	616	537	422	343	287	245	214
SU2200XLCD	5 BP48V60RT-3U	5982	4015	2407	1708	1318	1069	897	770	673	531	433	364	312	273
SU2200XLCD	6 BP48V60RT-3U	6846	4662	2831	2022	1567	1275	1072	923	809	640	524	441	379	332
SU2200XLCD	7 BP48V60RT-3U	7642	5273	3240	2329	1811	1478	1246	1075	943	749	614	518	447	392
SU2200XLCD	8 BP48V60RT-3U	8377	5851	3636	2628	2051	1678	1417	1224	1076	857	704	595	514	451
SU2200XLCD	9 BP48V60RT-3U	9057	6400	4019	2920	2286	1875	1586	1373	1208	964	793	672	581	511
SU2200XLCD	10 BP48V60RT-3U	9690	6920	4390	3205	2518	2069	1754	1519	1339	1070	882	749	648	571

All runtime values are shown in minutes.