



SU3000RTXL2U Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in WATTS													
			50	100	250	500	750	1,000	1,350	1,500	1,700	1,900	2,100	2,300	2,500	2,700
SU3000RTXL2U	Included Batteries	0	369	218	91	43	27	19	13.8	11.9	9.9	8.4	7.2	6.2	5.5	4.8
SU3000RTXL2U	BP72V15-2U	1	1,009	619	271	130	81	58	40	35	30	26	22	20	18	16
SU3000RTXL2U	BP72V18-2US	1	1,166	719	318	154	97	69	48	42	36	31	27	24	21	19
SU3000RTXL2U	BP72V18-2US	2	1,925	1,213	556	277	178	128	90	79	68	59	52	46	42	38
SU3000RTXL2U	BP72V18-2US	3	2,642	1,690	792	403	263	191	135	119	102	89	79	71	64	58
SU3000RTXL2U	BP72V18-2US	4	3,319	2,150	1,025	529	348	255	182	161	139	121	107	96	87	79
SU3000RTXL2U	BP72V18-2US	5	3,959	2,594	1,254	655	434	320	230	203	176	154	137	123	111	101
SU3000RTXL2U	BP72V18-2US	6	4,566	3,023	1,479	780	520	385	278	246	213	187	167	150	135	123
SU3000RTXL2U	BP72V18-2US	7	5,141	3,436	1,701	904	606	450	326	290	251	221	197	177	160	146
SU3000RTXL2U	BP72V18-2US	8	5,688	3,836	1,919	1,028	691	515	375	333	289	255	227	205	186	170
SU3000RTXL2U	BP72V18-2US	9	6,207	4,222	2,134	1,150	776	580	424	377	328	289	258	233	211	193
SU3000RTXL2U	BP72V18-2US	10	6,702	4,596	2,345	1,271	861	645	472	421	366	324	289	261	237	217
SU3000RTXL2U	BP72V28-3U	1	1,627	1,018	461	227	145	104	73	64	54	47	42	37	33	30
SU3000RTXL2U	BP72V28-3U	2	2,780	1,783	839	428	280	204	145	128	110	96	85	76	68	62
SU3000RTXL2U	BP72V28-3U	3	3,834	2,507	1,208	630	417	307	220	195	168	147	131	117	106	96
SU3000RTXL2U	BP72V28-3U	4	4,799	3,190	1,569	830	554	411	297	264	228	201	179	160	145	133
SU3000RTXL2U	BP72V28-3U	5	5,688	3,836	1,919	1,028	691	515	375	333	289	255	227	205	186	170
SU3000RTXL2U	BP72V28-3U	6	6,507	4,448	2,261	1,223	827	619	453	403	351	310	277	249	227	207
SU3000RTXL2U	BP72V28-3U	7	7,266	5,028	2,593	1,415	962	722	531	473	413	365	326	295	268	245
SU3000RTXL2U	BP72V28-3U	8	7,970	5,579	2,916	1,604	1,095	825	608	543	474	420	376	340	310	284
SU3000RTXL2U	BP72V28-3U	9	8,626	6,103	3,232	1,791	1,228	928	686	613	536	475	426	385	351	322
SU3000RTXL2U	BP72V28-3U	10	9,237	6,602	3,538	1,975	1,359	1,029	763	682	597	530	476	431	393	361

All runtime values are shown in minutes.