



SU3000RTXL3U Estimated Runtime

| UPS | Battery Pack | BP qty | Load in Watts | | | | | | | | | | | | | |
|--------------|--------------------|--------|---------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | 100 | 200 | 300 | 400 | 600 | 800 | 1,000 | 1,200 | 1,400 | 1,600 | 1,800 | 2,000 | 2,200 | 2,400 |
| SU3000RTXL3U | Internal batteries | 0 | 220 | 114 | 74 | 53 | 33 | 23 | 18 | 14 | 11 | 9.3 | 7.8 | 6.7 | 5.7 | 5.0 |
| SU3000RTXL3U | BP72V15-2U | 1 | 629 | 342 | 229 | 169 | 107 | 77 | 59 | 47 | 39 | 33 | 28 | 25 | 22 | 19 |
| SU3000RTXL3U | BP72V18-2US | 1 | 731 | 401 | 269 | 199 | 127 | 91 | 70 | 56 | 46 | 39 | 34 | 30 | 26 | 23 |
| SU3000RTXL3U | BP72V18-2US | 2 | 1,232 | 693 | 474 | 355 | 232 | 169 | 131 | 106 | 88 | 75 | 65 | 57 | 50 | 45 |
| SU3000RTXL3U | BP72V18-2US | 3 | 1,716 | 982 | 678 | 513 | 339 | 249 | 194 | 158 | 132 | 113 | 98 | 86 | 77 | 69 |
| SU3000RTXL3U | BP72V18-2US | 4 | 2,182 | 1,264 | 880 | 670 | 446 | 330 | 259 | 212 | 178 | 152 | 133 | 117 | 105 | 94 |
| SU3000RTXL3U | BP72V18-2US | 5 | 2,631 | 1,542 | 1,080 | 826 | 554 | 412 | 325 | 266 | 224 | 193 | 168 | 149 | 133 | 120 |
| SU3000RTXL3U | BP72V18-2US | 6 | 3,065 | 1,813 | 1,277 | 980 | 661 | 494 | 391 | 321 | 271 | 233 | 204 | 181 | 162 | 147 |
| SU3000RTXL3U | BP72V18-2US | 7 | 3,484 | 2,079 | 1,472 | 1,133 | 768 | 575 | 457 | 376 | 318 | 275 | 241 | 214 | 192 | 173 |
| SU3000RTXL3U | BP72V18-2US | 8 | 3,888 | 2,340 | 1,663 | 1,284 | 874 | 657 | 523 | 432 | 366 | 316 | 278 | 247 | 222 | 201 |
| SU3000RTXL3U | BP72V18-2US | 9 | 4,278 | 2,595 | 1,852 | 1,434 | 980 | 738 | 589 | 487 | 413 | 358 | 315 | 280 | 252 | 228 |
| SU3000RTXL3U | BP72V18-2US | 10 | 4,656 | 2,845 | 2,038 | 1,582 | 1,085 | 819 | 654 | 542 | 461 | 400 | 352 | 313 | 282 | 256 |
| SU3000RTXL3U | BP72V28RT3U | 1 | 1,034 | 577 | 392 | 293 | 189 | 137 | 106 | 85 | 71 | 60 | 52 | 46 | 40 | 36 |
| SU3000RTXL3U | BP72V28RT3U | 2 | 1,810 | 1,039 | 719 | 544 | 360 | 265 | 207 | 168 | 141 | 121 | 105 | 92 | 82 | 74 |
| SU3000RTXL3U | BP72V28RT3U | 3 | 2,543 | 1,487 | 1,041 | 795 | 533 | 395 | 312 | 255 | 215 | 184 | 161 | 142 | 127 | 115 |
| SU3000RTXL3U | BP72V28RT3U | 4 | 3,234 | 1,920 | 1,355 | 1,042 | 704 | 526 | 417 | 343 | 290 | 250 | 219 | 194 | 174 | 157 |
| SU3000RTXL3U | BP72V28RT3U | 5 | 3,888 | 2,340 | 1,663 | 1,284 | 874 | 657 | 523 | 432 | 366 | 316 | 278 | 247 | 222 | 201 |
| SU3000RTXL3U | BP72V28RT3U | 6 | 4,506 | 2,745 | 1,964 | 1,523 | 1,043 | 787 | 628 | 520 | 442 | 383 | 337 | 300 | 270 | 245 |
| SU3000RTXL3U | BP72V28RT3U | 7 | 5,092 | 3,138 | 2,258 | 1,757 | 1,209 | 916 | 733 | 608 | 518 | 450 | 396 | 353 | 318 | 289 |
| SU3000RTXL3U | BP72V28RT3U | 8 | 5,649 | 3,518 | 2,545 | 1,987 | 1,374 | 1,043 | 837 | 696 | 594 | 516 | 456 | 407 | 367 | 334 |
| SU3000RTXL3U | BP72V28RT3U | 9 | 6,177 | 3,886 | 2,825 | 2,213 | 1,536 | 1,170 | 941 | 784 | 670 | 583 | 515 | 461 | 416 | 378 |
| SU3000RTXL3U | BP72V28RT3U | 10 | 6,680 | 4,243 | 3,099 | 2,436 | 1,697 | 1,295 | 1,044 | 871 | 745 | 649 | 574 | 514 | 465 | 423 |

All runtime values are shown in minutes.