



## SU3000RTXL3UN Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	300	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,200	2,400
SU3000RTXL3UN	Internal batteries	0	220	114	74	53	33	23	18	14	11	9.3	7.8	6.7	5.7	5.0
SU3000RTXL3UN	BP72V15-2U	1	629	342	229	169	107	77	59	47	39	33	28	25	22	19
SU3000RTXL3UN	BP72V18-2US	1	731	401	269	199	127	91	70	56	46	39	34	30	26	23
SU3000RTXL3UN	BP72V18-2US	2	1,232	693	474	355	232	169	131	106	88	75	65	57	50	45
SU3000RTXL3UN	BP72V18-2US	3	1,716	982	678	513	339	249	194	158	132	113	98	86	77	69
SU3000RTXL3UN	BP72V18-2US	4	2,182	1,264	880	670	446	330	259	212	178	152	133	117	105	94
SU3000RTXL3UN	BP72V18-2US	5	2,631	1,542	1,080	826	554	412	325	266	224	193	168	149	133	120
SU3000RTXL3UN	BP72V18-2US	6	3,065	1,813	1,277	980	661	494	391	321	271	233	204	181	162	147
SU3000RTXL3UN	BP72V18-2US	7	3,484	2,079	1,472	1,133	768	575	457	376	318	275	241	214	192	173
SU3000RTXL3UN	BP72V18-2US	8	3,888	2,340	1,663	1,284	874	657	523	432	366	316	278	247	222	201
SU3000RTXL3UN	BP72V18-2US	9	4,278	2,595	1,852	1,434	980	738	589	487	413	358	315	280	252	228
SU3000RTXL3UN	BP72V18-2US	10	4,656	2,845	2,038	1,582	1,085	819	654	542	461	400	352	313	282	256
SU3000RTXL3UN	BP72V28RT3U	1	1,034	577	392	293	189	137	106	85	71	60	52	46	40	36
SU3000RTXL3UN	BP72V28RT3U	2	1,810	1,039	719	544	360	265	207	168	141	121	105	92	82	74
SU3000RTXL3UN	BP72V28RT3U	3	2,543	1,487	1,041	795	533	395	312	255	215	184	161	142	127	115
SU3000RTXL3UN	BP72V28RT3U	4	3,234	1,920	1,355	1,042	704	526	417	343	290	250	219	194	174	157
SU3000RTXL3UN	BP72V28RT3U	5	3,888	2,340	1,663	1,284	874	657	523	432	366	316	278	247	222	201
SU3000RTXL3UN	BP72V28RT3U	6	4,506	2,745	1,964	1,523	1,043	787	628	520	442	383	337	300	270	245
SU3000RTXL3UN	BP72V28RT3U	7	5,092	3,138	2,258	1,757	1,209	916	733	608	518	450	396	353	318	289
SU3000RTXL3UN	BP72V28RT3U	8	5,649	3,518	2,545	1,987	1,374	1,043	837	696	594	516	456	407	367	334
SU3000RTXL3UN	BP72V28RT3U	9	6,177	3,886	2,825	2,213	1,536	1,170	941	784	670	583	515	461	416	378
SU3000RTXL3UN	BP72V28RT3U	10	6,680	4,243	3,099	2,436	1,697	1,295	1,044	871	745	649	574	514	465	423

All runtime values are shown in minutes.