



SU3000RTXLCD2U Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	300	400	600	800	1,000	1,300	1,500	1,700	2,000	2,200	2,500	2,700
SU3000RTXLCD2U	Internal batteries	0	227	117	76	54	33	23	17	12	9.7	8.1	6.4	5.6	4.6	4.1
SU3000RTXLCD2U	BP72V15-2U	1	652	357	239	177	113	81	62	45	37	31	25	22	19	17
SU3000RTXLCD2U	BP72V18-2US	1	758	418	282	209	134	96	74	54	45	38	30	27	23	20
SU3000RTXLCD2U	BP72V18-2US	2	1,275	722	495	372	243	177	137	101	84	72	58	52	44	40
SU3000RTXLCD2U	BP72V18-2US	3	1,774	1,021	707	536	355	261	204	151	127	109	89	79	67	61
SU3000RTXLCD2U	BP72V18-2US	4	2,254	1,314	917	699	467	346	272	203	171	147	120	107	91	83
SU3000RTXLCD2U	BP72V18-2US	5	2,717	1,601	1,125	861	579	431	340	256	216	186	153	136	116	106
SU3000RTXLCD2U	BP72V18-2US	6	3,162	1,881	1,329	1,022	691	516	409	309	262	226	186	166	142	129
SU3000RTXLCD2U	BP72V18-2US	7	3,592	2,156	1,530	1,180	802	602	478	362	307	265	219	196	168	153
SU3000RTXLCD2U	BP72V18-2US	8	4,006	2,425	1,729	1,337	912	687	547	415	353	306	253	226	194	177
SU3000RTXLCD2U	BP72V18-2US	9	4,406	2,688	1,924	1,492	1,022	771	615	469	399	346	287	257	221	202
SU3000RTXLCD2U	BP72V18-2US	10	4,792	2,946	2,117	1,646	1,131	855	684	522	445	386	321	288	248	227
SU3000RTXLCD2U	BP72V28RT3U	1	1,070	601	409	306	199	144	111	82	68	58	47	41	35	32
SU3000RTXLCD2U	BP72V28RT3U	2	1,871	1,080	749	569	377	278	217	162	136	116	95	84	72	65
SU3000RTXLCD2U	BP72V28RT3U	3	2,625	1,544	1,083	829	557	414	327	245	207	178	146	130	111	101
SU3000RTXLCD2U	BP72V28RT3U	4	3,336	1,992	1,410	1,085	735	551	437	330	280	241	199	178	152	139
SU3000RTXLCD2U	BP72V28RT3U	5	4,006	2,425	1,729	1,337	912	687	547	415	353	306	253	226	194	177
SU3000RTXLCD2U	BP72V28RT3U	6	4,639	2,843	2,040	1,585	1,087	822	657	501	427	370	307	275	237	217
SU3000RTXLCD2U	BP72V28RT3U	7	5,238	3,248	2,344	1,828	1,260	956	766	586	501	435	362	325	280	256
SU3000RTXLCD2U	BP72V28RT3U	8	5,806	3,639	2,640	2,066	1,431	1,089	874	671	574	500	417	374	324	296
SU3000RTXLCD2U	BP72V28RT3U	9	6,345	4,018	2,930	2,300	1,600	1,220	982	755	648	565	471	424	367	336
SU3000RTXLCD2U	BP72V28RT3U	10	6,857	4,384	3,213	2,529	1,766	1,351	1,089	840	721	629	526	473	411	377

All runtime values are shown in minutes.