



SU3000RTXLCD2UN Estimated Runtime

| UPS | External Battery Pack | BP QTY | CONNECTED EQUIPMENT LOAD IN WATTS | | | | | | | | | | | | | |
|-----------------|-----------------------|--------|-----------------------------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | 100 | 200 | 300 | 400 | 500 | 600 | 800 | 1,000 | 1,200 | 1,500 | 1,800 | 2,100 | 2,400 | 2,700 |
| SU3000RTXLCD2UN | Internal batteries | n/a | 227 | 117 | 76 | 54 | 41 | 33 | 23 | 17 | 13 | 9.7 | 7.5 | 6.0 | 4.9 | 4.1 |
| SU3000RTXLCD2UN | BP72V15-2U | 1 | 652 | 357 | 239 | 177 | 138 | 113 | 81 | 62 | 49 | 37 | 29 | 24 | 20 | 17 |
| SU3000RTXLCD2UN | BP72V18-2US | 1 | 758 | 418 | 282 | 209 | 164 | 134 | 96 | 74 | 59 | 45 | 35 | 29 | 24 | 20 |
| SU3000RTXLCD2UN | BP72V18-2US | 2 | 1,275 | 722 | 495 | 372 | 295 | 243 | 177 | 137 | 111 | 84 | 67 | 55 | 46 | 40 |
| SU3000RTXLCD2UN | BP72V18-2US | 3 | 1,774 | 1,021 | 707 | 536 | 428 | 355 | 261 | 204 | 166 | 127 | 101 | 83 | 70 | 61 |
| SU3000RTXLCD2UN | BP72V18-2US | 4 | 2,254 | 1,314 | 917 | 699 | 562 | 467 | 346 | 272 | 222 | 171 | 137 | 113 | 96 | 83 |
| SU3000RTXLCD2UN | BP72V18-2US | 5 | 2,717 | 1,601 | 1,125 | 861 | 694 | 579 | 431 | 340 | 279 | 216 | 173 | 144 | 122 | 106 |
| SU3000RTXLCD2UN | BP72V18-2US | 6 | 3,162 | 1,881 | 1,329 | 1,022 | 826 | 691 | 516 | 409 | 337 | 262 | 211 | 175 | 149 | 129 |
| SU3000RTXLCD2UN | BP72V18-2US | 7 | 3,592 | 2,156 | 1,530 | 1,180 | 957 | 802 | 602 | 478 | 394 | 307 | 248 | 207 | 176 | 153 |
| SU3000RTXLCD2UN | BP72V18-2US | 8 | 4,006 | 2,425 | 1,729 | 1,337 | 1,087 | 912 | 687 | 547 | 452 | 353 | 286 | 239 | 204 | 177 |
| SU3000RTXLCD2UN | BP72V18-2US | 9 | 4,406 | 2,688 | 1,924 | 1,492 | 1,215 | 1,022 | 771 | 615 | 510 | 399 | 324 | 271 | 232 | 202 |
| SU3000RTXLCD2UN | BP72V18-2US | 10 | 4,792 | 2,946 | 2,117 | 1,646 | 1,342 | 1,131 | 855 | 684 | 567 | 445 | 362 | 303 | 260 | 227 |
| SU3000RTXLCD2UN | BP72V28-3U | 1 | 1,070 | 601 | 409 | 306 | 242 | 199 | 144 | 111 | 90 | 68 | 54 | 44 | 37 | 32 |
| SU3000RTXLCD2UN | BP72V28-3U | 2 | 1,871 | 1,080 | 749 | 569 | 455 | 377 | 278 | 217 | 177 | 136 | 108 | 89 | 75 | 65 |
| SU3000RTXLCD2UN | BP72V28-3U | 3 | 2,625 | 1,544 | 1,083 | 829 | 668 | 557 | 414 | 327 | 268 | 207 | 166 | 138 | 117 | 101 |
| SU3000RTXLCD2UN | BP72V28-3U | 4 | 3,336 | 1,992 | 1,410 | 1,085 | 879 | 735 | 551 | 437 | 360 | 280 | 226 | 188 | 160 | 139 |
| SU3000RTXLCD2UN | BP72V28-3U | 5 | 4,006 | 2,425 | 1,729 | 1,337 | 1,087 | 912 | 687 | 547 | 452 | 353 | 286 | 239 | 204 | 177 |
| SU3000RTXLCD2UN | BP72V28-3U | 6 | 4,639 | 2,843 | 2,040 | 1,585 | 1,292 | 1,087 | 822 | 657 | 544 | 427 | 347 | 290 | 249 | 217 |
| SU3000RTXLCD2UN | BP72V28-3U | 7 | 5,238 | 3,248 | 2,344 | 1,828 | 1,494 | 1,260 | 956 | 766 | 636 | 501 | 408 | 342 | 294 | 256 |
| SU3000RTXLCD2UN | BP72V28-3U | 8 | 5,806 | 3,639 | 2,640 | 2,066 | 1,693 | 1,431 | 1,089 | 874 | 728 | 574 | 469 | 394 | 339 | 296 |
| SU3000RTXLCD2UN | BP72V28-3U | 9 | 6,345 | 4,018 | 2,930 | 2,300 | 1,889 | 1,600 | 1,220 | 982 | 819 | 648 | 530 | 446 | 384 | 336 |
| SU3000RTXLCD2UN | BP72V28-3U | 10 | 6,857 | 4,384 | 3,213 | 2,529 | 2,082 | 1,766 | 1,351 | 1,089 | 910 | 721 | 591 | 498 | 430 | 377 |

All runtime values are shown in minutes.