



SU3000RTXLCDN Estimated Runtime

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	300	400	500	600	800	1,000	1,200	1,500	1,800	2,100	2,400	2,700
SU3000RTXLCDN	Internal batteries	n/a	221	115	74	53	41	32	22	17	13	9.5	7.3	5.8	4.8	4.0
SU3000RTXLCDN	BP72V15-2U	1	637	351	235	174	136	111	79	61	49	37	29	23	20	17
SU3000RTXLCDN	BP72V18-2US	1	740	410	277	206	162	132	95	73	58	44	35	28	24	20
SU3000RTXLCDN	BP72V18-2US	2	1,247	709	487	366	291	239	175	135	110	83	66	54	45	39
SU3000RTXLCDN	BP72V18-2US	3	1,736	1,003	696	528	422	350	257	201	164	125	100	82	69	60
SU3000RTXLCDN	BP72V18-2US	4	2,207	1,291	903	689	554	461	341	268	219	169	135	112	94	81
SU3000RTXLCDN	BP72V18-2US	5	2,661	1,574	1,108	849	685	571	426	336	276	213	171	142	120	104
SU3000RTXLCDN	BP72V18-2US	6	3,099	1,851	1,309	1,007	815	682	510	404	332	258	208	173	147	127
SU3000RTXLCDN	BP72V18-2US	7	3,521	2,122	1,508	1,164	944	792	594	472	389	304	245	204	174	151
SU3000RTXLCDN	BP72V18-2US	8	3,929	2,387	1,704	1,319	1,072	901	678	540	446	349	282	236	201	175
SU3000RTXLCDN	BP72V18-2US	9	4,323	2,646	1,897	1,472	1,199	1,009	762	608	503	394	320	268	229	199
SU3000RTXLCDN	BP72V18-2US	10	4,703	2,900	2,087	1,624	1,325	1,117	845	676	560	440	358	300	257	224
SU3000RTXLCDN	BP72V28-3U	1	1,046	590	403	302	239	196	142	110	89	67	53	43	36	31
SU3000RTXLCDN	BP72V28-3U	2	1,832	1,061	738	560	449	372	274	214	175	134	107	88	74	64
SU3000RTXLCDN	BP72V28-3U	3	2,572	1,518	1,067	817	659	549	409	322	264	204	164	136	115	100
SU3000RTXLCDN	BP72V28-3U	4	3,270	1,960	1,389	1,070	867	726	544	431	355	276	223	185	158	137
SU3000RTXLCDN	BP72V28-3U	5	3,929	2,387	1,704	1,319	1,072	901	678	540	446	349	282	236	201	175
SU3000RTXLCDN	BP72V28-3U	6	4,553	2,799	2,011	1,563	1,275	1,074	812	649	538	422	343	287	245	214
SU3000RTXLCDN	BP72V28-3U	7	5,143	3,199	2,311	1,803	1,475	1,245	944	757	629	495	403	338	290	253
SU3000RTXLCDN	BP72V28-3U	8	5,704	3,585	2,604	2,039	1,671	1,413	1,075	864	719	568	463	389	335	292
SU3000RTXLCDN	BP72V28-3U	9	6,236	3,959	2,890	2,270	1,865	1,580	1,206	971	810	640	524	441	379	332
SU3000RTXLCDN	BP72V28-3U	10	6,742	4,321	3,170	2,497	2,056	1,745	1,335	1,077	899	713	584	492	424	372

All runtime values are shown in minutes.