



SU3000RTXLCD3U Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	300	400	600	800	1,000	1,300	1,500	1,700	2,000	2,200	2,500	2,700
SU3000RTXLCD3U	Internal batteries	0	221	115	74	53	32	22	17	12	9.5	7.9	6.3	5.4	4.5	4.0
SU3000RTXLCD3U	BP72V15-2U	1	637	351	235	174	111	79	61	44	37	31	25	22	18	17
SU3000RTXLCD3U	BP72V18-2US	1	740	410	277	206	132	95	73	53	44	37	30	26	22	20
SU3000RTXLCD3U	BP72V18-2US	2	1,247	709	487	366	239	175	135	100	83	71	58	51	43	39
SU3000RTXLCD3U	BP72V18-2US	3	1,736	1,003	696	528	350	257	201	149	125	107	87	77	66	60
SU3000RTXLCD3U	BP72V18-2US	4	2,207	1,291	903	689	461	341	268	200	169	145	119	105	90	81
SU3000RTXLCD3U	BP72V18-2US	5	2,661	1,574	1,108	849	571	426	336	252	213	183	151	134	115	104
SU3000RTXLCD3U	BP72V18-2US	6	3,099	1,851	1,309	1,007	682	510	404	305	258	223	183	163	140	127
SU3000RTXLCD3U	BP72V18-2US	7	3,521	2,122	1,508	1,164	792	594	472	357	304	262	216	193	166	151
SU3000RTXLCD3U	BP72V18-2US	8	3,929	2,387	1,704	1,319	901	678	540	410	349	302	250	223	192	175
SU3000RTXLCD3U	BP72V18-2US	9	4,323	2,646	1,897	1,472	1,009	762	608	463	394	342	283	253	218	199
SU3000RTXLCD3U	BP72V18-2US	10	4,703	2,900	2,087	1,624	1,117	845	676	516	440	382	317	284	245	224
SU3000RTXLCD3U	BP72V28RT3U	1	1,046	590	403	302	196	142	110	81	67	57	46	41	34	31
SU3000RTXLCD3U	BP72V28RT3U	2	1,832	1,061	738	560	372	274	214	159	134	115	94	83	71	64
SU3000RTXLCD3U	BP72V28RT3U	3	2,572	1,518	1,067	817	549	409	322	242	204	176	144	128	110	100
SU3000RTXLCD3U	BP72V28RT3U	4	3,270	1,960	1,389	1,070	726	544	431	326	276	238	196	175	150	137
SU3000RTXLCD3U	BP72V28RT3U	5	3,929	2,387	1,704	1,319	901	678	540	410	349	302	250	223	192	175
SU3000RTXLCD3U	BP72V28RT3U	6	4,553	2,799	2,011	1,563	1,074	812	649	495	422	366	303	272	234	214
SU3000RTXLCD3U	BP72V28RT3U	7	5,143	3,199	2,311	1,803	1,245	944	757	579	495	430	357	320	277	253
SU3000RTXLCD3U	BP72V28RT3U	8	5,704	3,585	2,604	2,039	1,413	1,075	864	663	568	494	412	369	319	292
SU3000RTXLCD3U	BP72V28RT3U	9	6,236	3,959	2,890	2,270	1,580	1,206	971	747	640	558	466	419	362	332
SU3000RTXLCD3U	BP72V28RT3U	10	6,742	4,321	3,170	2,497	1,745	1,335	1,077	830	713	622	520	468	405	372

All runtime values are shown in minutes.