



SU3000RTXR3UHW Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	300	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,200	2,400
SU3000RTXR3UHW	Internal batteries	0	472	251	165	119	74	51	38	30	25	21	18	15	14	12
SU3000RTXR3UHW	BP72V15-2U	1	883	489	330	246	158	114	88	71	58	50	43	37	33	30
SU3000RTXR3UHW	BP72V18-2US	1	984	547	371	277	179	129	100	80	67	57	49	43	38	34
SU3000RTXR3UHW	BP72V18-2US	2	1,476	838	576	434	285	208	162	131	110	93	81	71	63	57
SU3000RTXR3UHW	BP72V18-2US	3	1,951	1,124	780	592	393	289	226	185	155	132	115	102	91	81
SU3000RTXR3UHW	BP72V18-2US	4	2,409	1,404	981	748	500	371	292	239	201	172	150	133	119	107
SU3000RTXR3UHW	BP72V18-2US	5	2,850	1,678	1,179	903	608	453	358	294	247	213	186	165	148	133
SU3000RTXR3UHW	BP72V18-2US	6	3,276	1,947	1,375	1,057	715	535	424	349	295	254	223	197	177	160
SU3000RTXR3UHW	BP72V18-2US	7	3,687	2,210	1,568	1,209	821	616	490	404	342	295	259	230	207	187
SU3000RTXR3UHW	BP72V18-2US	8	4,085	2,468	1,758	1,359	927	698	556	459	390	337	296	263	237	214
SU3000RTXR3UHW	BP72V18-2US	9	4,469	2,720	1,945	1,508	1,032	779	621	515	437	379	333	297	267	242
SU3000RTXR3UHW	BP72V18-2US	10	4,840	2,968	2,130	1,655	1,137	859	687	570	485	420	370	330	297	270
SU3000RTXR3UHW	BP72V28RT3U	1	1,281	722	494	371	242	176	137	111	92	78	68	60	53	48
SU3000RTXR3UHW	BP72V28RT3U	2	2,044	1,180	820	623	414	306	239	195	164	140	122	108	96	87
SU3000RTXR3UHW	BP72V28RT3U	3	2,763	1,624	1,140	872	586	436	344	283	238	205	179	158	142	128
SU3000RTXR3UHW	BP72V28RT3U	4	3,442	2,053	1,452	1,118	758	567	450	371	314	271	237	211	189	171
SU3000RTXR3UHW	BP72V28RT3U	5	4,085	2,468	1,758	1,359	927	698	556	459	390	337	296	263	237	214
SU3000RTXR3UHW	BP72V28RT3U	6	4,693	2,869	2,057	1,597	1,095	827	661	548	466	404	355	317	285	259
SU3000RTXR3UHW	BP72V28RT3U	7	5,269	3,258	2,348	1,830	1,261	956	765	636	542	470	415	370	333	303
SU3000RTXR3UHW	BP72V28RT3U	8	5,817	3,634	2,633	2,058	1,425	1,083	870	724	618	537	474	424	382	348
SU3000RTXR3UHW	BP72V28RT3U	9	6,337	3,999	2,912	2,283	1,587	1,209	973	811	693	604	534	477	431	392
SU3000RTXR3UHW	BP72V28RT3U	10	6,833	4,352	3,184	2,504	1,747	1,334	1,076	898	769	670	593	531	480	437

All runtime values are shown in minutes.