



SU3000XLCD Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			100	200	300	400	600	800	1,000	1,300	1,500	1,700	2,000	2,200	2,500	2,700
SU3000XLCD	Internal batteries	0	226	119	78	56	35	25	19	14	11	9.2	7.0	6.0	4.7	4.1
SU3000XLCD	BP72V15-2U	1	643	354	238	176	112	81	62	45	37	31	25	22	19	17
SU3000XLCD	BP72V18-2US	1	747	415	280	208	134	96	74	54	45	38	30	27	23	20
SU3000XLCD	BP72V18-2US	2	1,258	716	492	370	242	177	137	101	84	72	58	52	44	40
SU3000XLCD	BP72V18-2US	3	1,750	1,013	704	534	354	261	204	151	127	109	89	79	67	61
SU3000XLCD	BP72V18-2US	4	2,225	1,304	913	697	466	345	272	203	171	147	120	107	91	83
SU3000XLCD	BP72V18-2US	5	2,682	1,589	1,119	858	578	431	340	256	216	186	153	136	116	106
SU3000XLCD	BP72V18-2US	6	3,123	1,868	1,323	1,018	690	516	409	309	262	226	186	166	142	129
SU3000XLCD	BP72V18-2US	7	3,548	2,141	1,523	1,176	801	601	478	362	307	265	219	196	168	153
SU3000XLCD	BP72V18-2US	8	3,958	2,408	1,721	1,333	911	686	546	415	353	306	253	226	194	177
SU3000XLCD	BP72V18-2US	9	4,354	2,670	1,916	1,488	1,020	770	615	469	399	346	287	257	221	202
SU3000XLCD	BP72V18-2US	10	4,737	2,926	2,107	1,641	1,129	854	684	522	445	386	321	288	248	227
SU3000XLCD	BP72V28RT3U	1	1,055	596	407	305	198	144	111	82	68	58	47	41	35	32
SU3000XLCD	BP72V28RT3U	2	1,846	1,072	746	567	376	277	217	162	136	116	95	84	72	65
SU3000XLCD	BP72V28RT3U	3	2,592	1,533	1,078	826	556	414	326	245	207	178	146	130	111	101
SU3000XLCD	BP72V28RT3U	4	3,295	1,978	1,403	1,082	734	550	436	330	280	241	199	178	152	139
SU3000XLCD	BP72V28RT3U	5	3,958	2,408	1,721	1,333	911	686	546	415	353	306	253	226	194	177
SU3000XLCD	BP72V28RT3U	6	4,585	2,824	2,031	1,580	1,085	821	656	501	427	370	307	275	237	217
SU3000XLCD	BP72V28RT3U	7	5,179	3,227	2,333	1,822	1,258	955	765	586	501	435	362	325	280	256
SU3000XLCD	BP72V28RT3U	8	5,742	3,616	2,629	2,059	1,429	1,087	874	671	574	500	417	374	324	296
SU3000XLCD	BP72V28RT3U	9	6,277	3,992	2,917	2,293	1,597	1,219	982	755	648	565	471	424	367	336
SU3000XLCD	BP72V28RT3U	10	6,785	4,357	3,199	2,522	1,763	1,349	1,089	840	721	629	526	473	411	377

All runtime values are shown in minutes.