



SU40KX Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in Watts													
			2,100	4,400	6,700	9,000	11,250	13,500	16,000	18,500	20,500	22,500	25,000	27,500	29,500	32,000
SU40KX	Included Batteries	0	142.6	64.2	39.1	27.2	20.7	16.3	13.0	11.0	9.8	8.7	7.6	6.8	6.2	5.5
SU40KX	BP480V26B	1	361.8	165.1	101.3	70.9	54.0	42.6	34.3	29.1	25.8	23.1	20.4	18.1	16.6	14.9
SU40KX	BP480V40C	1	499.0	233.0	144.8	102.1	78.3	62.1	50.2	42.8	38.1	34.2	30.2	27.0	24.8	22.4
SU40KX	BP480V200	1	647.1	308.2	193.8	137.8	106.2	84.7	68.6	58.7	52.4	47.2	41.8	37.4	34.4	31.2
SU40KX	BP480V300	1	873.1	425.4	271.4	194.9	151.3	121.3	98.8	84.8	75.9	68.5	60.9	54.6	50.3	45.7
SU40KX	BP480V400	1	1115.7	553.6	357.2	258.7	202.1	162.9	133.3	114.8	103.0	93.1	82.9	74.5	68.8	62.7
SU40KX	BP480V500	1	1467.8	742.6	485.1	354.6	279.0	226.2	186.2	160.9	144.8	131.3	117.2	105.6	97.7	89.2
SU40KX	BP480V300	2	1617.3	823.8	540.5	396.3	312.6	254.0	209.5	181.3	163.3	148.2	132.5	119.5	110.6	101.0
SU40KX	BP480V400	2	2073.9	1075.3	713.0	526.9	418.2	341.6	283.2	246.0	222.1	202.1	181.2	163.8	151.9	139.1
SU40KX	BP480V500	2	2720.9	1439.7	965.6	719.6	574.7	472.2	393.5	343.3	310.9	283.6	255.0	231.2	214.9	197.2
SU40KX	BP480V400	3	2965.5	1579.9	1063.5	794.6	635.9	523.4	436.9	381.6	345.9	315.8	284.3	258.0	240.0	220.4
SU40KX	BP480V500	3	3858.2	2103.1	1432.2	1078.7	868.5	718.6	602.9	528.6	480.4	439.7	397.0	361.4	336.8	310.0
SU40KX	BP480V500	4	4894.3	2733.6	1883.3	1429.3	1157.2	962.1	810.7	713.2	649.8	596.1	539.7	492.4	459.7	424.1

All runtime values are shown in minutes.