



## SU5000RT4U Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			1,200	1,400	1,600	1,800	2,000	2,200	2,400	2,600	2,800	3,000	3,200	3,400	3,600	3,800
SU5000RT4U	INCLUDED BATTERIES	0	30	24	19	15	13	12	10	9.5	8.7	8.0	7.4	6.9	6.4	6.0
SU5000RT4U	BP192V5RT2U	1	75	63	53	46	41	36	32	29	26	24	22	20	19	17
SU5000RT4U	BP192V12-3U	1	130	109	94	82	72	64	57	51	47	43	39	36	34	31
SU5000RT4U	BP192V12-3U	2	230	194	167	147	130	115	104	94	86	78	72	67	62	58
SU5000RT4U	BP192V12-3U	3	332	282	244	215	190	170	153	139	127	117	108	100	93	87
SU5000RT4U	BP192V12-3U	4	435	371	322	284	252	226	204	185	170	156	145	134	125	117
SU5000RT4U	BP192V12-3U	5	537	459	400	353	315	282	255	233	213	197	182	170	159	149
SU5000RT4U	BP192V12-3U	6	640	548	478	423	378	339	307	280	257	238	221	205	192	180
SU5000RT4U	BP192V12-3U	7	742	637	557	493	441	396	359	328	302	279	259	242	226	212
SU5000RT4U	BP192V12-3U	8	844	725	635	563	504	453	412	377	346	321	298	278	260	245
SU5000RT4U	BP192V12-3U	9	944	813	712	633	567	511	464	425	391	362	337	315	295	277
SU5000RT4U	BP192V12-3U	10	1,045	901	790	702	629	568	516	473	436	404	376	351	329	310
SU5000RT4U	BP192V787C-1PH	1	630	539	471	416	371	333	302	276	253	234	217	202	189	177
SU5000RT4U	BP192V787C-1PH	2	1,282	1,108	974	868	779	704	642	589	543	504	470	439	413	389
SU5000RT4U	BP192V787C-1PH	3	1,906	1,656	1,463	1,308	1,179	1,069	977	899	832	774	723	678	638	602
SU5000RT4U	BP192V787C-1PH	4	2,500	2,182	1,934	1,735	1,568	1,425	1,305	1,203	1,116	1,040	973	914	861	814
SU5000RT4U	BP192V787C-1PH	5	3,068	2,686	2,388	2,148	1,945	1,772	1,626	1,501	1,394	1,301	1,219	1,146	1,081	1,023

All runtime values are shown in minutes.