



SU5000RT4UTF Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			600	900	1,200	1,500	1,800	2,100	2,400	2,700	3,000	3,300	3,600	3,900	4,200	4,500
SU5000RT4UTF	INCLUDED BATTERIES	0	58	36	25	19	15	12	10	8.3	7.1	6.0	5.2	4.5	4.0	3.5
SU5000RT4UTF	BP192V5RT2U	1	131	84	60	46	37	30	26	22	19	17	15	14	12	11
SU5000RT4UTF	BP192V12-3U	1	238	155	113	87	70	58	49	43	37	33	29	27	24	22
SU5000RT4UTF	BP192V12-3U	2	426	284	209	163	133	111	95	82	72	64	57	52	47	43
SU5000RT4UTF	BP192V12-3U	3	615	414	308	242	198	167	143	124	109	97	88	79	72	66
SU5000RT4UTF	BP192V12-3U	4	803	545	408	323	265	224	192	168	148	132	119	108	99	91
SU5000RT4UTF	BP192V12-3U	5	988	675	508	404	333	282	243	212	188	168	152	138	126	116
SU5000RT4UTF	BP192V12-3U	6	1,172	805	608	485	401	340	294	257	228	204	185	168	154	142
SU5000RT4UTF	BP192V12-3U	7	1,352	934	707	566	469	399	345	303	269	241	218	199	183	168
SU5000RT4UTF	BP192V12-3U	8	1,531	1,061	806	646	537	458	397	348	310	278	252	230	211	195
SU5000RT4UTF	BP192V12-3U	9	1,707	1,188	905	727	605	516	448	394	351	316	286	261	240	222
SU5000RT4UTF	BP192V12-3U	10	1,881	1,313	1,002	807	673	575	500	440	392	353	320	293	269	249
SU5000RT4UTF	BP192V787C-1PH	1	1,179	810	612	488	404	343	296	259	230	206	186	170	155	143
SU5000RT4UTF	BP192V787C-1PH	2	2,312	1,626	1,248	1,009	844	723	630	556	497	448	407	373	344	318
SU5000RT4UTF	BP192V787C-1PH	3	3,351	2,394	1,857	1,512	1,273	1,097	960	851	763	690	630	579	535	497
SU5000RT4UTF	BP192V787C-1PH	4	4,306	3,118	2,438	1,997	1,689	1,461	1,283	1,140	1,025	930	851	783	725	674
SU5000RT4UTF	BP192V787C-1PH	5	5,186	3,800	2,993	2,465	2,092	1,815	1,598	1,424	1,283	1,166	1,068	985	913	851

All runtime values are shown in minutes.