



SU5000RT4UTFTAA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			200	400	600	800	1,000	1,200	1,500	1,800	2,000	2,500	3,000	3,500	4,000	4,500
SU5000RT4UTFTAA	Included batteries	0	176	91	58	42	32	25	19	15	13	9.4	7.1	5.5	4.3	3.5
SU5000RT4UTFTAA	BP192V5RT2U	1	368	198	131	96	74	60	46	37	32	24	19	16	13	11
SU5000RT4UTFTAA	BP192V12RT3UTAA	1	639	354	238	176	138	113	87	70	62	47	37	31	26	22
SU5000RT4UTFTAA	BP192V12RT3UTAA	2	1096	622	426	320	254	209	163	133	118	90	72	59	50	43
SU5000RT4UTFTAA	BP192V12RT3UTAA	3	1538	888	615	466	372	308	242	198	176	136	109	91	77	66
SU5000RT4UTFTAA	BP192V12RT3UTAA	4	1967	1150	803	612	491	408	323	265	236	184	148	123	105	91
SU5000RT4UTFTAA	BP192V12RT3UTAA	5	2381	1406	988	756	609	508	404	333	297	232	188	157	134	116
SU5000RT4UTFTAA	BP192V12RT3UTAA	6	2782	1658	1172	900	727	608	485	401	359	281	228	191	163	142
SU5000RT4UTFTAA	BP192V12RT3UTAA	7	3170	1906	1352	1042	844	707	566	469	420	330	269	226	193	168
SU5000RT4UTFTAA	BP192V12RT3UTAA	8	3546	2148	1531	1183	961	806	646	537	482	379	310	260	224	195
SU5000RT4UTFTAA	BP192V12RT3UTAA	9	3911	2386	1707	1323	1076	905	727	605	543	429	351	295	254	222
SU5000RT4UTFTAA	BP192V12RT3UTAA	10	4264	2620	1881	1461	1191	1002	807	673	604	478	392	331	285	249
SU5000RT4UTFTAA	BP192V787C-1PH	1	2978	1783	1262	971	786	658	525	435	389	305	248	208	178	155
SU5000RT4UTFTAA	BP192V787C-1PH	2	5261	3294	2388	1867	1529	1292	1045	874	787	626	515	436	377	331
SU5000RT4UTFTAA	BP192V787C-1PH	3	7147	4635	3421	2705	2233	1899	1547	1302	1177	943	781	665	577	509
SU5000RT4UTFTAA	BP192V787C-1PH	4	8731	5832	4370	3489	2899	2478	2031	1718	1556	1253	1043	892	777	687
SU5000RT4UTFTAA	BP192V787C-1PH	5	10080	6907	5246	4223	3531	3031	2497	2120	1925	1557	1301	1115	974	863

All runtime values are shown in minutes.