



## SU6000RT4U Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			300	600	900	1,200	1,500	1,800	2,100	2,400	2,700	3,000	3,300	3,600	3,900	4,200
SU6000RT4U	INCLUDED BATTERIES	0	213	103	64	44	33	25	20	17	14	13	11	9.9	8.9	8.0
SU6000RT4U	BP192V5RT2U	1	360	184	119	86	66	53	44	37	32	28	25	22	20	18
SU6000RT4U	BP192V12-3U	1	559	293	193	141	109	88	73	62	54	47	42	38	34	31
SU6000RT4U	BP192V12-3U	2	897	483	322	238	187	152	127	109	95	83	74	67	60	55
SU6000RT4U	BP192V12-3U	3	1,228	672	453	338	266	218	184	158	137	121	108	98	89	81
SU6000RT4U	BP192V12-3U	4	1,551	859	585	438	347	286	241	208	182	161	144	130	118	108
SU6000RT4U	BP192V12-3U	5	1,867	1,044	715	538	428	354	300	259	227	201	180	163	149	136
SU6000RT4U	BP192V12-3U	6	2,175	1,227	845	638	510	422	358	310	272	242	217	197	179	165
SU6000RT4U	BP192V12-3U	7	2,475	1,408	973	738	591	490	417	361	318	283	254	231	211	193
SU6000RT4U	BP192V12-3U	8	2,769	1,586	1,101	837	671	558	476	413	364	324	292	265	242	223
SU6000RT4U	BP192V12-3U	9	3,056	1,761	1,227	935	752	626	535	464	410	365	329	299	274	252
SU6000RT4U	BP192V12-3U	10	3,335	1,935	1,352	1,033	832	694	593	516	456	407	367	334	305	281
SU6000RT4U	BP192V787C-1PH	1	2,098	1,182	812	613	489	405	344	297	261	232	208	188	172	157
SU6000RT4U	BP192V787C-1PH	2	3,942	2,316	1,630	1,251	1,011	846	725	632	559	500	452	411	377	348
SU6000RT4U	BP192V787C-1PH	3	5,531	3,357	2,399	1,861	1,515	1,276	1,099	963	855	768	696	636	585	541
SU6000RT4U	BP192V787C-1PH	4	6,915	4,313	3,124	2,443	2,002	1,693	1,464	1,286	1,146	1,032	938	859	791	733
SU6000RT4U	BP192V787C-1PH	5	8,131	5,195	3,807	2,999	2,470	2,097	1,819	1,603	1,431	1,291	1,176	1,078	995	924

All runtime values are shown in minutes.