



SU6000RT4UHVG Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			1,500	1,800	2,100	2,400	2,700	3,000	3,300	3,600	3,900	4,200	4,500	4,800	5,100	5,400
SU6000RT4UHVG	INCLUDED BATTERIES	0	19	15	12	10	8.5	7.1	5.9	5.0	4.3	3.7	3.2	2.7	2.3	2.0
SU6000RT4UHVG	BP192V5RT2U	1	45	36	30	25	22	19	17	15	13	12	11	10	9	9
SU6000RT4UHVG	BP192V12-3U	1	85	69	57	49	42	37	33	29	26	24	22	20	18	17
SU6000RT4UHVG	BP192V12-3U	2	160	130	109	93	81	71	63	57	51	47	43	39	36	34
SU6000RT4UHVG	BP192V12-3U	3	238	195	164	140	122	108	96	86	78	71	66	60	56	52
SU6000RT4UHVG	BP192V12-3U	4	317	260	220	189	166	146	131	118	107	98	90	83	77	72
SU6000RT4UHVG	BP192V12-3U	5	397	327	277	239	210	185	166	150	136	125	115	106	99	92
SU6000RT4UHVG	BP192V12-3U	6	476	394	334	289	254	225	202	182	166	152	140	130	121	113
SU6000RT4UHVG	BP192V12-3U	7	556	461	392	340	299	265	238	216	197	180	166	154	143	134
SU6000RT4UHVG	BP192V12-3U	8	635	528	450	390	344	306	275	249	227	209	193	179	166	156
SU6000RT4UHVG	BP192V12-3U	9	715	595	507	441	389	346	312	283	258	237	219	203	190	177
SU6000RT4UHVG	BP192V12-3U	10	793	661	565	492	434	387	348	316	289	266	246	228	213	199
SU6000RT4UHVG	BP192V787C-1PH	1	480	397	337	291	256	227	203	184	167	153	141	131	122	114
SU6000RT4UHVG	BP192V787C-1PH	2	992	830	711	620	549	491	443	402	369	339	314	292	273	256
SU6000RT4UHVG	BP192V787C-1PH	3	1,488	1,252	1,079	946	841	754	682	623	572	528	491	458	428	402
SU6000RT4UHVG	BP192V787C-1PH	4	1,967	1,662	1,437	1,264	1,127	1,013	920	841	774	716	666	623	584	549
SU6000RT4UHVG	BP192V787C-1PH	5	2,428	2,060	1,787	1,576	1,408	1,269	1,153	1,056	974	903	841	787	738	696

All runtime values are shown in minutes.