



## SU6000RTFMB Estimated Runtime

UPS	Extended Battery Module	EBM QTY	CONNECTED EQUIPMENT LOAD IN WATTS								
			540	945	1,350	2,025	2,700	3,375	4,050	4,725	5,400
SU6000RTFMB	Internal batteries	0	57.0	39.0	22.0	15.0	8.5	6.0	4.5	3.7	3.0
SU6000RTFMB	BP180RT	1	203.0	144.0	85.0	61.0	38.0	31.0	24.0	20.0	16.0
SU6000RTFMB	BP180RT	2	399.0	273.0	147.0	109.0	71.0	58.0	45.0	36.0	28.0
SU6000RTFMB	BP180RT	3	554.0	384.0	214.0	159.0	104.0	83.0	62.0	54.0	47.0
SU6000RTFMB	BP180RT	4	755.0	521.0	287.0	210.0	133.0	111.0	90.0	74.0	58.0

*All runtime values are shown in minutes.*