



## SU6000RTMB Estimated Runtime

| UPS        | Extended Battery Module | EBM QTY | CONNECTED EQUIPMENT LOAD IN WATTS |       |       |       |       |       |       |       |       |
|------------|-------------------------|---------|-----------------------------------|-------|-------|-------|-------|-------|-------|-------|-------|
|            |                         |         | 540                               | 945   | 1,350 | 2,025 | 2,700 | 3,375 | 4,050 | 4,725 | 5,400 |
| SU6000RTMB | Internal batteries      | 0       | 57.0                              | 39.0  | 22.0  | 15.0  | 8.5   | 6.0   | 4.5   | 3.7   | 3.0   |
| SU6000RTMB | BP180RT                 | 1       | 203.0                             | 144.0 | 85.0  | 61.0  | 38.0  | 31.0  | 24.0  | 20.0  | 16.0  |
| SU6000RTMB | BP180RT                 | 2       | 399.0                             | 273.0 | 147.0 | 109.0 | 71.0  | 58.0  | 45.0  | 36.0  | 28.0  |
| SU6000RTMB | BP180RT                 | 3       | 554.0                             | 384.0 | 214.0 | 159.0 | 104.0 | 83.0  | 62.0  | 54.0  | 47.0  |
| SU6000RTMB | BP180RT                 | 4       | 755.0                             | 521.0 | 287.0 | 210.0 | 133.0 | 111.0 | 90.0  | 74.0  | 58.0  |

*All runtime values are shown in minutes.*