



## SU750RTXL2U Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			20	30	50	100	150	200	250	300	350	400	450	500	550	600
SU750RTXL2U	Internal batteries	0	189	145	96	48	29	20	15	11	8.9	7.3	6.2	5.3	4.6	4.0
SU750RTXL2U	BP24V15RT2U	1	647	514	360	197	131	96	75	61	50	42	36	32	28	25
SU750RTXL2U	BP24V28-2U	1	1,096	879	625	352	239	178	140	114	95	80	69	61	54	48
SU750RTXL2U	BP24V36-2US	1	1,315	1,059	756	430	294	219	173	142	118	100	87	76	68	61
SU750RTXL2U	BP24V36-2US	2	2,361	1,925	1,399	818	570	432	346	286	240	206	180	159	142	128
SU750RTXL2U	BP24V36-2US	3	3,326	2,735	2,012	1,198	844	646	520	433	366	316	276	245	220	199
SU750RTXL2U	BP24V36-2US	4	4,219	3,496	2,597	1,568	1,113	858	694	581	492	426	374	333	300	272
SU750RTXL2U	BP24V36-2US	5	5,046	4,210	3,156	1,928	1,378	1,067	867	727	619	537	473	422	380	345
SU750RTXL2U	BP24V36-2US	6	5,815	4,882	3,689	2,278	1,638	1,273	1,037	873	744	647	571	510	460	419
SU750RTXL2U	BP24V36-2US	7	6,532	5,515	4,200	2,618	1,892	1,476	1,206	1,017	869	757	669	598	541	492
SU750RTXL2U	BP24V36-2US	8	7,202	6,113	4,688	2,949	2,142	1,676	1,373	1,160	992	866	766	686	621	566
SU750RTXL2U	BP24V36-2US	9	7,829	6,678	5,156	3,271	2,387	1,873	1,537	1,301	1,115	974	863	774	701	640
SU750RTXL2U	BP24V36-2US	10	8,418	7,214	5,604	3,585	2,627	2,067	1,700	1,441	1,237	1,081	960	861	780	713
SU750RTXL2U	BP24V70-3U	1	2,361	1,925	1,399	818	570	432	346	286	240	206	180	159	142	128
SU750RTXL2U	BP24V70-3U	2	4,219	3,496	2,597	1,568	1,113	858	694	581	492	426	374	333	300	272
SU750RTXL2U	BP24V70-3U	3	5,815	4,882	3,689	2,278	1,638	1,273	1,037	873	744	647	571	510	460	419
SU750RTXL2U	BP24V70-3U	4	7,202	6,113	4,688	2,949	2,142	1,676	1,373	1,160	992	866	766	686	621	566
SU750RTXL2U	BP24V70-3U	5	8,418	7,214	5,604	3,585	2,627	2,067	1,700	1,441	1,237	1,081	960	861	780	713
SU750RTXL2U	BP24V70-3U	6	9,492	8,204	6,448	4,189	3,093	2,446	2,019	1,716	1,477	1,294	1,150	1,034	939	858
SU750RTXL2U	BP24V70-3U	7	10,449	9,100	7,228	4,762	3,542	2,814	2,331	1,986	1,713	1,503	1,339	1,205	1,095	1,003
SU750RTXL2U	BP24V70-3U	8	11,306	9,913	7,950	5,307	3,974	3,171	2,634	2,250	1,944	1,710	1,524	1,374	1,250	1,146
SU750RTXL2U	BP24V70-3U	9	12,078	10,656	8,621	5,825	4,391	3,518	2,931	2,509	2,172	1,913	1,707	1,541	1,403	1,287
SU750RTXL2U	BP24V70-3U	10	12,777	11,336	9,247	6,320	4,792	3,854	3,220	2,762	2,395	2,112	1,888	1,706	1,554	1,427

All runtime values are shown in minutes.