



SU750RTLCD2U Estimated Runtime

UPS	Battery Pack	Load in Watts													
		20	60	100	160	200	260	300	360	400	460	500	560	600	675
SU750RTLCD2U	INCLUDED BATTERIES	190	85	52	32	25	19	16	13	11	8.5	7.4	6.1	5.4	4.3
SU750RTLCD2U	1 BP24V15RT2U	636	302	191	119	93	69	59	47	41	34	31	27	24	21
SU750RTLCD2U	1 BP24V28-2U	1078	529	341	216	172	129	110	89	78	66	59	51	47	40
SU750RTLCD2U	1 BP24V36-2US	1295	643	417	266	212	160	137	111	98	82	74	65	59	51
SU750RTLCD2U	2 BP24V36-2US	2326	1198	795	520	419	321	276	227	201	171	155	135	124	107
SU750RTLCD2U	3 BP24V36-2US	3279	1733	1166	772	626	484	419	346	308	263	239	210	194	167
SU750RTLCD2U	4 BP24V36-2US	4161	2247	1527	1021	832	647	562	466	416	356	325	286	265	229
SU750RTLCD2U	5 BP24V36-2US	4980	2740	1878	1266	1035	809	704	586	524	450	411	363	336	292
SU750RTLCD2U	6 BP24V36-2US	5742	3215	2220	1506	1236	969	846	706	632	544	498	440	408	356
SU750RTLCD2U	7 BP24V36-2US	6453	3671	2553	1742	1433	1128	986	824	739	638	584	517	480	419
SU750RTLCD2U	8 BP24V36-2US	7117	4110	2877	1974	1628	1285	1124	942	846	731	670	595	552	483
SU750RTLCD2U	9 BP24V36-2US	7740	4532	3193	2202	1820	1440	1262	1059	952	824	756	671	624	546
SU750RTLCD2U	10 BP24V36-2US	8325	4940	3500	2426	2009	1593	1398	1176	1057	917	841	748	696	610
SU750RTLCD2U	1 BP24V70-3U	2326	1198	795	520	419	321	276	227	201	171	155	135	124	107
SU750RTLCD2U	2 BP24V70-3U	4161	2247	1527	1021	832	647	562	466	416	356	325	286	265	229
SU750RTLCD2U	3 BP24V70-3U	5742	3215	2220	1506	1236	969	846	706	632	544	498	440	408	356
SU750RTLCD2U	4 BP24V70-3U	7117	4110	2877	1974	1628	1285	1124	942	846	731	670	595	552	483
SU750RTLCD2U	5 BP24V70-3U	8325	4940	3500	2426	2009	1593	1398	1176	1057	917	841	748	696	610
SU750RTLCD2U	6 BP24V70-3U	9394	5711	4092	2861	2379	1895	1666	1405	1265	1100	1011	900	838	736
SU750RTLCD2U	7 BP24V70-3U	10346	6431	4655	3282	2738	2189	1929	1630	1471	1280	1178	1051	980	862
SU750RTLCD2U	8 BP24V70-3U	11201	7103	5191	3688	3087	2477	2186	1852	1673	1459	1343	1200	1119	986
SU750RTLCD2U	9 BP24V70-3U	11971	7732	5701	4080	3426	2758	2438	2070	1872	1635	1507	1347	1258	1110
SU750RTLCD2U	10 BP24V70-3U	12670	8323	6188	4460	3756	3033	2685	2284	2068	1809	1668	1493	1395	1232

All runtime values are shown in minutes.