



SU750XL Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			20	30	50	100	150	200	250	300	350	400	450	500	550	600
SU750XL	Internal batteries	0	189	145	96	48	29	20	15	11	8.9	7.3	6.2	5.3	4.6	4.0
SU750XL	BP24V15RT2U	1	647	514	360	197	131	96	75	61	50	42	36	32	28	25
SU750XL	BP24V28-2U	1	1,096	879	625	352	239	178	140	114	95	80	69	61	54	48
SU750XL	BP24V36-2US	1	1,315	1,059	756	430	294	219	173	142	118	100	87	76	68	61
SU750XL	BP24V36-2US	2	2,361	1,925	1,399	818	570	432	346	286	240	206	180	159	142	128
SU750XL	BP24V36-2US	3	3,326	2,735	2,012	1,198	844	646	520	433	366	316	276	245	220	199
SU750XL	BP24V36-2US	4	4,219	3,496	2,597	1,568	1,113	858	694	581	492	426	374	333	300	272
SU750XL	BP24V36-2US	5	5,046	4,210	3,156	1,928	1,378	1,067	867	727	619	537	473	422	380	345
SU750XL	BP24V36-2US	6	5,815	4,882	3,689	2,278	1,638	1,273	1,037	873	744	647	571	510	460	419
SU750XL	BP24V36-2US	7	6,532	5,515	4,200	2,618	1,892	1,476	1,206	1,017	869	757	669	598	541	492
SU750XL	BP24V36-2US	8	7,202	6,113	4,688	2,949	2,142	1,676	1,373	1,160	992	866	766	686	621	566
SU750XL	BP24V36-2US	9	7,829	6,678	5,156	3,271	2,387	1,873	1,537	1,301	1,115	974	863	774	701	640
SU750XL	BP24V36-2US	10	8,418	7,214	5,604	3,585	2,627	2,067	1,700	1,441	1,237	1,081	960	861	780	713

All runtime values are shown in minutes.