



## SU8000RT3UG Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			700	1,200	1,700	2,200	2,700	3,200	3,700	4,200	4,700	5,200	5,700	6,200	6,700	7,200
SU8000RT3UG	INCLUDED BATTERIES	0	115	61	39	28	21	16	13	11	9.6	8.4	7.5	6.7	6.0	5.5
SU8000RT3UG	BP240V10RT3U	1	268	151	102	75	59	48	40	34	29	26	23	20	18	17
SU8000RT3UG	BP240V10RT3U	2	420	242	165	123	97	79	66	57	49	43	39	35	31	29
SU8000RT3UG	BP240V10RT3U	3	573	335	231	173	137	113	95	81	71	62	55	50	45	41
SU8000RT3UG	BP240V10RT3U	4	725	428	297	225	179	147	124	107	93	82	73	66	60	55
SU8000RT3UG	BP240V10RT3U	5	875	521	364	276	221	182	154	133	116	103	92	83	75	69
SU8000RT3UG	BP240V10RT3U	6	1,025	614	431	329	263	218	185	159	139	124	111	100	91	83
SU8000RT3UG	BP240V10RT3U	7	1,172	707	499	381	306	254	216	186	163	145	130	117	107	98
SU8000RT3UG	BP240V10RT3U	8	1,319	799	566	433	349	290	247	213	187	166	149	135	123	113
SU8000RT3UG	BP240V10RT3U	9	1,463	891	633	486	392	326	278	241	212	188	169	153	140	128
SU8000RT3UG	BP240V10RT3U	10	1,607	982	699	538	435	363	310	268	236	210	189	171	156	144
SU8000RT3UG	BP240V787C-1PH	1	1,270	769	543	416	334	278	236	204	179	159	143	129	118	108
SU8000RT3UG	BP240V787C-1PH	2	2,478	1,547	1,116	868	706	594	510	445	393	352	318	289	265	244
SU8000RT3UG	BP240V787C-1PH	3	3,579	2,283	1,667	1,307	1,072	906	782	685	609	547	495	452	416	384
SU8000RT3UG	BP240V787C-1PH	4	4,585	2,977	2,196	1,734	1,429	1,213	1,051	924	823	741	673	616	567	525
SU8000RT3UG	BP240V787C-1PH	5	5,508	3,634	2,703	2,146	1,776	1,513	1,314	1,158	1,034	933	849	778	718	665

All runtime values are shown in minutes.