



SU8000RT4U Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Watts													
			400	800	1,200	1,600	2,000	2,400	2,800	3,200	3,600	4,000	4,400	4,800	5,200	5,600
SU8000RT4U	INCLUDED BATTERIES	0	155	72	43	29	21	16	12	10	8.8	7.7	6.8	6.1	5.5	5.0
SU8000RT4U	BP192V5RT2U	1	269	133	85	61	46	37	31	26	22	19	17	15	14	12
SU8000RT4U	BP192V12-3U	1	422	214	138	100	77	62	51	43	38	33	29	26	23	21
SU8000RT4U	BP192V12-3U	2	684	357	235	171	133	108	90	77	66	58	52	46	42	38
SU8000RT4U	BP192V12-3U	3	943	501	333	245	192	156	131	112	97	86	76	69	62	57
SU8000RT4U	BP192V12-3U	4	1,198	645	432	320	252	206	173	148	129	114	102	92	83	76
SU8000RT4U	BP192V12-3U	5	1,449	787	531	396	313	256	216	186	162	144	128	116	105	96
SU8000RT4U	BP192V12-3U	6	1,694	929	630	471	373	307	260	224	196	173	155	140	128	117
SU8000RT4U	BP192V12-3U	7	1,936	1,069	728	547	434	358	303	262	229	204	183	165	150	138
SU8000RT4U	BP192V12-3U	8	2,172	1,208	826	622	496	409	347	300	264	234	210	190	174	159
SU8000RT4U	BP192V12-3U	9	2,405	1,345	923	697	556	461	391	339	298	265	238	216	197	181
SU8000RT4U	BP192V12-3U	10	2,633	1,481	1,020	772	617	512	436	377	332	296	266	241	220	203
SU8000RT4U	BP192V787C-1PH	1	1,633	894	605	452	358	295	249	214	187	166	148	134	122	112
SU8000RT4U	BP192V787C-1PH	2	3,131	1,783	1,235	939	754	627	535	464	410	365	329	299	274	252
SU8000RT4U	BP192V787C-1PH	3	4,462	2,615	1,838	1,411	1,141	955	819	715	633	567	513	468	429	396
SU8000RT4U	BP192V787C-1PH	4	5,652	3,394	2,415	1,868	1,519	1,277	1,099	963	855	768	696	636	585	541
SU8000RT4U	BP192V787C-1PH	5	6,723	4,125	2,965	2,308	1,886	1,591	1,374	1,206	1,074	966	878	803	740	685

All runtime values are shown in minutes.