



SU80K Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in Watts													
			5,500	10,000	14,500	19,000	23,500	28,000	32,500	37,000	41,500	46,000	50,500	55,000	59,500	64,000
SU80K	BP480V40C	1	144	73	47	34	26	21	17	14	12	11	9	8	7	7
SU80K	BP480V200	1	209	108	70	50	39	31	26	22	19	16	15	13	12	11
SU80K	BP480V300	1	311	164	107	78	60	49	40	34	30	26	23	21	19	17
SU80K	BP480V400	1	423	227	150	109	85	69	57	49	42	37	33	30	27	24
SU80K	BP480V500	1	588	321	214	158	123	100	84	72	62	55	49	44	40	36
SU80K	BP480V300	2	659	362	243	179	140	114	96	82	71	63	56	50	46	42
SU80K	BP480V400	2	881	490	332	247	195	159	134	115	100	89	79	71	65	59
SU80K	BP480V500	2	1202	679	465	349	277	228	192	166	145	129	115	104	95	87
SU80K	BP480V400	3	1326	753	517	389	309	255	215	186	163	145	130	117	107	98
SU80K	BP480V500	3	1791	1032	715	542	434	359	305	265	233	207	186	169	154	141
SU80K	BP480V500	4	2354	1377	963	735	591	492	420	365	322	287	259	235	215	198

All runtime values are shown in minutes.