



SU80KX2 Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in Watts													
			5,500	10,000	14,500	19,000	23,500	28,000	32,500	37,000	41,500	46,000	50,500	55,000	59,500	64,000
SU80KX2	BP480V40C	2	312	167	110	80	62	50	42	35	30	27	24	21	19	17
SU80KX2	BP480V200	1	203	107	69	50	39	31	26	22	19	16	14	13	11	10
SU80KX2	BP480V200	2	443	241	161	118	92	75	62	53	46	40	36	32	29	26
SU80KX2	BP480V200	3	683	380	257	191	150	122	102	87	76	67	59	53	48	44
SU80KX2	BP480V200	4	920	520	355	265	210	172	145	124	108	95	85	77	69	63
SU80KX2	BP480V300	1	303	162	107	78	60	48	40	34	29	26	23	20	18	17
SU80KX2	BP480V300	2	644	357	241	179	140	114	96	82	71	62	55	50	45	41
SU80KX2	BP480V300	3	980	555	379	284	225	185	156	133	116	103	92	83	75	68
SU80KX2	BP480V300	4	1309	752	519	392	312	257	218	187	164	145	130	117	107	98
SU80KX2	BP480V400	1	412	224	149	109	85	69	57	49	42	37	33	29	26	24
SU80KX2	BP480V400	2	860	484	330	246	194	159	134	115	100	88	78	71	64	58
SU80KX2	BP480V400	3	1296	744	513	387	308	254	215	185	162	143	128	116	105	96
SU80KX2	BP480V400	4	1719	1001	697	529	424	351	299	258	226	201	180	163	149	136
SU80KX2	BP480V500	1	574	317	213	157	123	100	84	71	62	54	48	43	39	36
SU80KX2	BP480V500	2	1175	671	462	348	276	227	192	165	144	128	114	103	93	85
SU80KX2	BP480V500	3	1752	1020	711	540	433	359	305	264	231	205	184	167	152	139
SU80KX2	BP480V500	4	2304	1362	957	732	590	491	420	364	320	285	257	233	213	196

All runtime values are shown in minutes.