



SUINT1000LCD2UN Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in WATTS													
			20	40	60	80	100	150	200	300	400	500	600	700	800	900
SUINT1000LCD2UN	Included Batteries	0	240	152	109	84	67	44	32	20	14	11	8.4	6.7	5.6	4.7
SUINT1000LCD2UN	BP24V15RT2U	1	682	447	328	256	208	139	102	65	46	35	28	23	19	16
SUINT1000LCD2UN	BP24V28-2U	1	1,117	745	553	436	358	243	181	116	84	64	51	42	36	31
SUINT1000LCD2UN	BP24V70-3U	1	2,345	1,607	1,216	974	809	563	427	283	207	161	130	109	93	80
SUINT1000LCD2UN	BP24V70-3U	2	4,154	2,929	2,255	1,829	1,536	1,089	839	567	424	334	273	230	198	173
SUINT1000LCD2UN	BP24V70-3U	3	5,715	4,120	3,215	2,632	2,225	1,598	1,241	850	641	509	420	355	307	269
SUINT1000LCD2UN	BP24V70-3U	4	7,076	5,199	4,103	3,385	2,878	2,087	1,631	1,128	856	684	566	481	417	367
SUINT1000LCD2UN	BP24V70-3U	5	8,273	6,181	4,927	4,093	3,497	2,558	2,011	1,400	1,068	857	712	607	528	465
SUINT1000LCD2UN	BP24V70-3U	6	9,334	7,077	5,694	4,760	4,086	3,012	2,379	1,667	1,277	1,029	857	732	638	564
SUINT1000LCD2UN	BP24V70-3U	7	10,280	7,900	6,409	5,389	4,646	3,449	2,737	1,929	1,483	1,198	1,000	856	747	662
SUINT1000LCD2UN	BP24V70-3U	8	11,130	8,656	7,078	5,983	5,179	3,871	3,085	2,186	1,686	1,366	1,142	980	856	759
SUINT1000LCD2UN	BP24V70-3U	9	11,897	9,355	7,704	6,545	5,687	4,277	3,422	2,437	1,886	1,531	1,283	1,102	964	856
SUINT1000LCD2UN	BP24V70-3U	10	12,593	10,003	8,292	7,078	6,172	4,670	3,751	2,683	2,083	1,694	1,422	1,223	1,072	952
SUINT1000LCD2UN	BP24V36-2US	1	1,330	892	665	527	434	296	221	143	103	79	64	53	45	38
SUINT1000LCD2UN	BP24V36-2US	2	2,345	1,607	1,216	974	809	563	427	283	207	161	130	109	93	80
SUINT1000LCD2UN	BP24V36-2US	3	3,284	2,286	1,746	1,408	1,177	828	634	425	315	247	201	169	144	126
SUINT1000LCD2UN	BP24V36-2US	4	4,154	2,929	2,255	1,829	1,536	1,089	839	567	424	334	273	230	198	173
SUINT1000LCD2UN	BP24V36-2US	5	4,962	3,540	2,745	2,237	1,885	1,346	1,041	709	532	422	346	292	252	221
SUINT1000LCD2UN	BP24V36-2US	6	5,715	4,120	3,215	2,632	2,225	1,598	1,241	850	641	509	420	355	307	269
SUINT1000LCD2UN	BP24V36-2US	7	6,418	4,673	3,668	3,014	2,556	1,845	1,437	989	748	597	493	418	362	318
SUINT1000LCD2UN	BP24V36-2US	8	7,076	5,199	4,103	3,385	2,878	2,087	1,631	1,128	856	684	566	481	417	367
SUINT1000LCD2UN	BP24V36-2US	9	7,693	5,701	4,523	3,744	3,192	2,325	1,822	1,265	962	771	639	544	472	416
SUINT1000LCD2UN	BP24V36-2US	10	8,273	6,181	4,927	4,093	3,497	2,558	2,011	1,400	1,068	857	712	607	528	465

All runtime values are shown in minutes.